



Product: [6303UE](#)

Security & Sound, #18-5c, BC, CMP

Product Description

Security & Sound Cable, Plenum-CMP 5-18 AWG stranded bare copper conductors with Flamarrest® insulation, Flamarrest® jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	5	18	7x26	BC - Bare Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.009 in (0.23 mm)	0.047 in (1.2 mm)	Black, Red, White, Green, Brown

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.203 in	Yes

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
6.79 Ohm/1000ft	30 pF/ft (98 pF/m)	4 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	0°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
2.03 in (51.6 mm)	2.03 in

Max. Pull Tension:	104 lbs (47.2 kg)
Bulk Cable Weight:	38 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Outdoor
----------------------------	---------

Flammability / Reaction to Fire:	NFPA 262 (UL910), FT6
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	5303UE

History

Update and Revision:	Revision Number: 0.299 Revision Date: 05-05-2023
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
6303UE 8771000	Natural	612825175445	C
6303UE 877U1000	Natural	612825175438	

© 2023 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.