



**Product:** [BIX PATCH CORDS](#)

BIX Patch Cords

## Product Description

BIX Patch Cords

## Technical Specifications

### Product Overview

Suitable Applications:	TIA Category 5
------------------------	----------------

### Physical Characteristics (Overall)

Packaging:	Individually packaged in a clear plastic bag.
------------	---

### Connectors

#### Materials

Description	Material	Color
Boot	PVC	Grey cameleon
Conductor	BC - Bare Copper	
Front Connection	Blades Phosphor Bronze with Tin Plating over Nickel	
Insulation	PO - Polyolefin	
Outer Jacket	PVC - Polyvinyl Chloride	

### Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm

### Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

### Mechanical Characteristics

Footprint/Type:	BIX
Plug /Jack Compatibility:	BIX

#### Termination Interface

Connection	Durabilities
Mated Connection	200 Cycles

### Standards

UL Rating:	Riser
CSA Rating:	FT4
TIA/EIA Compliance:	Category 5 - TIA 568-C.2, ISO/IEC 11801:2002 Ed.2 Amendment 2

## Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

## Flammability, LSOH, Toxicity Testing

Safety Listing:	ACA, c(UL)us Listed
-----------------	---------------------

## Related Part Numbers

Related Parts:	BIX Connectors - QCBIX1A/1A4 connectors, BIX accessories
----------------	--

## Variants

Item #	Length	UPC
A0410469	4 ft	611589000673
A0410494	4 ft	611589000727
A0410471	7 ft	611589000680
A0410495	7 ft	611589000734
A0410473	10 ft	611589000697
A0410496	10 ft	611589000741
A0410475	15 ft	611589000703
A0410497	15 ft	611589000758
A0410493	25 ft	611589000710

## History

Update and Revision:	Revision Number: 0.144 Revision Date: 03-04-2023
----------------------	--

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.