

SACC-EC-FS-8CON-M16/ 1,0 SCO - Device connector front mounting



1567801

<https://www.phoenixcontact.com/us/products/1567801>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, 8-position, Socket, straight, M12-SPEEDCON, coding: A, on free cable end, Front mounting, M16 x 1.5, Individual wires, cable length: 1 m, 0.25 mm², TPE litz wire, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) item no.: 1240085

Commercial data

Item number	1567801
Packing unit	1 pc
Minimum order quantity	50 pc
Sales key	AB24
Product key	ABQCFB
GTIN	4046356327268
Weight per piece (including packing)	42.8 g
Weight per piece (excluding packing)	42.8 g
Customs tariff number	85444290
Country of origin	DE

SACC-EC-FS-8CON-M16/ 1,0 SCO - Device connector front mounting



1567801

<https://www.phoenixcontact.com/us/products/1567801>

Technical data

Notes

General	Lock nut is included in the scope of delivery
---------	---

Mounting

Mounting type	Front mounting M16 x 1.5 With locking nut
Assembly instructions	With locking nut
Connection method	Individual wires

Product properties

Product type	Circular connectors (device side)
Number of positions	8
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated
Conductor material	Tin-plated Cu litz wires

Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V
Nominal current I_N	2 A
Max. conductor resistance	80 m Ω /m

Connection data

Conductor connection

Connection method	Individual wires
-------------------	------------------

SACC-EC-FS-8CON-M16/ 1,0 SCO - Device connector front mounting



1567801

<https://www.phoenixcontact.com/us/products/1567801>

Contact connection type	Socket
Conductor cross section	0.25 mm²

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

Connection 2

Head design	free cable end
-------------	----------------

Cable/line

Cable length	1 m
Cable type	TPE litz wire
Wire diameter incl. insulation	1.15 mm ±0.07 mm
Single wire, color	brown, blue, white, gray, pink, green, yellow, red
Conductor material	Tin-plated Cu litz wires
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Material wire insulation	TPE
Thickness, insulation	0.21 mm (Core insulation)
Nominal voltage, cable	300 V
Test voltage, cable	2000 V AC
Cable resistance	≤ 80 mΩ/m
Cable insulation resistance	≥ 20 MΩ*km

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-25 °C ... 90 °C (cable, fixed installation)


SACC-EC-FS-8CON-M16/ 1,0 SCO - Device connector
front mounting




1567801

<https://www.phoenixcontact.com/us/products/1567801>

Drawings



Dimensional drawing




SACC-EC-FS-8CON-M16/ 1,0 SCO - Device connector front mounting



1567801

<https://www.phoenixcontact.com/us/products/1567801>

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side

SACC-EC-FS-8CON-M16/ 1,0 SCO - Device connector front mounting



1567801

<https://www.phoenixcontact.com/us/products/1567801>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1567801>



UL Recognized

Approval ID: E118976-20100522

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	2 A	- 24	-



EAC

Approval ID: B.01687



cULus Recognized

Approval ID: E221474-20140616

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	2 A	24 - 22	-

SACC-EC-FS-8CON-M16/ 1,0 SCO - Device connector front mounting



1567801

<https://www.phoenixcontact.com/us/products/1567801>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 8.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-EC-FS-8CON-M16/ 1,0 SCO - Device connector front mounting



1567801

<https://www.phoenixcontact.com/us/products/1567801>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com