




zQSFP+/QSFP28

TE Internal #: 2333842-8  
QSFP28 Cable Assembly, 16 Positions, 13.12 ft [4 m], 25 Gb/s, Black  
Cable, Shielded, 26 AWG, .129 mm², Madison TurboTwin - Round  
Jacketed, QSFP28 Plug

[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies > QSFP28 to QSFP28 Cable Assembly: 26 AWG



Cable Assembly Type: **QSFP28**

Equalized: **No**

Wire Size: **.129 mm²**

Outside Cable Diameter: **9.53 mm [ .375 in ]**

[All QSFP28 to QSFP28 Cable Assembly: 26 AWG \(10\)](#)

Features

Product Type Features

Cable Assembly Category	High Speed, Industry Standard
Cable Assembly Type	QSFP28
Connector Type (End A)	QSFP28 Plug
Connector Type (End B)	QSFP28 Plug
Cable Style	Madison TurboTwin - Round Jacketed

Configuration Features

Number of Positions	16
Number of Pairs	8
Number of Signal Positions	16

Electrical Characteristics

Impedance	100 Ω
-----------	-------

Signal Characteristics

Data Rate	25 Gb/s
-----------	---------



Body Features

Equalized	No
Cable Color	Black
Cable Flammability Rating	CL2

Dimensions

Wire Size	.129 mm²
Outside Cable Diameter	9.53 mm[.375 in]

Operation/Application

Shielded	Yes
Halogen Free	No

Other

Cable Assembly Configuration	Double Ended
Cable Assembly Length	4 m[13.12 ft]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the



product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 <p>TE Part # 2170705-7 CAGE ASSY, QSFP28 1X1, SPRING, HS, LP</p>	 <p>TE Part # 2170747-6 CAGE ASSY, 1X4, QSFP28, SPRING, HS, LP</p>	 <p>TE Part # 2170806-5 CAGE ASSEMBLY, 1X2, QSFP28, SPRING, HS</p>	 <p>TE Part # 2-2170747-2 CAGE ASSY, 1X4, QSFP28, SPRING, HS, LP</p>
 <p>TE Part # 2170704-2 CAGE ASSY, QSFP28 1X1, SPRING, HS</p>	 <p>TE Part # 2227103-2 1X2 CAGE ASSY BHND BZL QSFP28</p>	 <p>TE Part # 2227103-1 1X2 CAGE ASSY BHND BZL QSFP28</p>	 <p>TE Part # 2170704-1 CAGE ASSY, QSFP28 1X1, SPRING, HS</p>
 <p>TE Part # 2170704-5 CAGE ASSY, QSFP28 1X1, SPRING, HS</p>	 <p>TE Part # 1551892-1 Cage Assy Behind Bezel QSFP28</p>	 <p>TE Part # 2227104-1 1X2 CAGE ASSY, BHND BEZEL, QSFP28</p>	 <p>TE Part # 2170703-7 CAGE ASSEMBLY, QSFP28 1X1, SPRING</p>
 <p>TE Part # 2170790-4 CAGE ASSY, 1X4, QSFP28, SPRING, HS, LP</p>	 <p>TE Part # 2170703-6 CAGE ASSEMBLY, QSFP28 1X1, SPRING</p>	 <p>TE Part # 1551891-1 Cage Assy, Behind Bezel, QSFP28</p>	 <p>TE Part # 1551920-1 zQSFP+ connector assembly</p>





TE Part # 2-2170808-3  
QSFP28, 1X2, CAGE ASSY, SPRING, HS, LP

TE Part # 2170704-4  
CAGE ASSY, QSFP28 1X1, SPRING, HS

TE Part # 2170806-2  
CAGE ASSEMBLY, 1X2, QSFP28, SPRING, HS

TE Part # 2170806-3  
CAGE ASSEMBLY, 1X2, QSFP28, SPRING, HS

Also in the Series | zQSFP+/QSFP28

Heat Sinks(1)

Pluggable I/O Cable Assemblies(81)

QSFP, QSFP+ & zQSPF+(425)

Customers Also Bought

TE Part #CB03374007  
Single Heavy Wall RW 200 E: Heat Shrink Tubing, 2:1 Shrink Ratio

TE Part #440129-8  
2.0MM,HSG,8POS

TE Part #2299806-1  
NRW NON-FABRIC CARRIER, SOCKET P0

TE Part #52197-1  
TERM, RING, SOLIS, 6, #10, T&R

TE Part #1734098-5  
Champ050 50p A/P RCPT 25CL PB

TE Part #2334236-4  
QSFP TO [4]SFP 25GIG 30AWG 2 METER

TE Part #2204740-1  
75A/POLE, DUAL POLE SLIDING POWER CONN

TE Part #2311291-1  
CA, BUSBAR MATING TO CORD END TML

TE Part #2354935-1  
CAGE ASSEMBLY, 1X4, QSFP28, TB



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2333842-8\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2333842-8\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2333842-8\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English