



Product: [8524](#)

Lead Wire, #22 Str TC, PVC Ins, TYPE MW MIL-W-76C-PVC

[Request Sample](#)

Product Description

Low Temp Plastic Lead Wire, 22AWG (7x30) Tinned Copper, PVC Insulation, TYPE MW MIL-W-76C-PVC 1000V 80C

Technical Specifications

Product Overview

|                        |                                                                                                                             |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Suitable Applications: | inter-connection circuits, internal wiring of computer and electronic equipments, (Type MW) MIL-W-76C-Low Temp applications |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------|

Construction Details

Conductor

| Element      | No. of Elements | Size   | Stranding | Material           |
|--------------|-----------------|--------|-----------|--------------------|
| Conductor(s) | 1               | 22 AWG | 7x30      | TC - Tinned Copper |

Insulation

| Material                 | Nom. Thickness     | Nom. Insulation Diameter |
|--------------------------|--------------------|--------------------------|
| PVC - Polyvinyl Chloride | 0.017 in (0.43 mm) | 0.064 in (1.6 mm)        |

|                                   |                   |
|-----------------------------------|-------------------|
| Overall Cable Diameter (Nominal): | 0.064 in (1.6 mm) |
|-----------------------------------|-------------------|

Electrical Characteristics

Electricals

| Nom. Conductor DCR | Max. Current                               |
|--------------------|--------------------------------------------|
| 16 Ohm/1000ft      | Single conductor in free air @ 30°C: 9.0 A |

Voltage

| UL Voltage Rating |
|-------------------|
| 1000 V RMS        |

Mechanical Characteristics

Temperature

| UL Temperature | Operating      |
|----------------|----------------|
| 80°C           | -40°C To +80°C |

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 0.64 in (16 mm) | 0.64 in (16 mm)   |

|                    |                 |
|--------------------|-----------------|
| Max. Pull Tension: | 11 lbs (5.0 kg) |
| Bulk Cable Weight: | 4 lbs/1000ft    |

Standards and Compliance

|                                |                                                                                                                           |
|--------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| Environmental Suitability:     | Outdoor                                                                                                                   |
| Sustainability:                | CA Prop 65                                                                                                                |
| Military Compliance:           | MIL-W-76C Type MWP                                                                                                        |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |

History

|                      |                                                  |
|----------------------|--------------------------------------------------|
| Update and Revision: | Revision Number: 0.477 Revision Date: 01-20-2023 |
|----------------------|--------------------------------------------------|

Part Numbers

Variants

| Item #       | Color       | Putup Type | Length   | UPC          | Footnote |
|--------------|-------------|------------|----------|--------------|----------|
| 8524 010100  | Black       | Reel       | 100 ft   | 612825212379 |          |
| 8524 0101000 | Black       | Reel       | 1,000 ft | 612825347873 | P        |
| 8524 0131000 | Blue, Dark  | Reel       | 1,000 ft | 612825212393 | P        |
| 8524 006100  | Blue, Light | Reel       | 100 ft   | 612825212256 |          |
| 8524 0061000 | Blue, Light | Reel       | 1,000 ft | 612825212263 | P        |
| 8524 001100  | Brown       | Reel       | 100 ft   | 612825212119 |          |
| 8524 0011000 | Brown       | Reel       | 1,000 ft | 612825212126 | P        |
| 8524 008100  | Gray        | Reel       | 100 ft   | 612825212300 |          |
| 8524 0081000 | Gray        | Reel       | 1,000 ft | 612825212317 | P        |
| 8524 005100  | Green, Dark | Reel       | 100 ft   | 612825212232 |          |
| 8524 0051000 | Green, Dark | Reel       | 1,000 ft | 612825212249 | P        |
| 8524 003100  | Orange      | Reel       | 100 ft   | 612825212171 |          |
| 8524 0031000 | Orange      | Reel       | 1,000 ft | 612825212188 | P        |
| 8524 002100  | Red         | Reel       | 100 ft   | 612825212157 |          |
| 8524 0021000 | Red         | Reel       | 1,000 ft | 612825347866 | P        |
| 8524 007100  | Violet      | Reel       | 100 ft   | 612825212287 |          |
| 8524 0071000 | Violet      | Reel       | 1,000 ft | 612825212294 | P        |
| 8524 009100  | White       | Reel       | 100 ft   | 612825212348 |          |
| 8524 0091000 | White       | Reel       | 1,000 ft | 612825212355 | P        |
| 8524 004100  | Yellow      | Reel       | 100 ft   | 612825212201 |          |
| 8524 0041000 | Yellow      | Reel       | 1,000 ft | 612825212218 | P        |

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.