



Product: <u>19349</u> ☑

Portable Cordage, 3 C #16 Str BC, PVC Ins, PVC Jkt, UL Type SJT

Request Sample

Product Description

Portable Cordage, 3 Conductor 16AWG (65x34) Bare Copper, PVC Insulation, PVC Outer Jacket, UL Type SJT

Technical Specifications

Product Overview					
Suitable Applications: Portable cordage and cordage					
Construction Details					
Conductor					
Element Number o	f Element	Size	Stranding	Material	
Conductor(s) 3		16	65x34	BC - Bare Copper	
Insulation					
Material	Nom. Thic	knes	s Nom. In	sulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.033 in (0.	84 mr	n) 0.123 in	(3.12 mm)	Green/Yellow, Black, White
Outer Jacket					
Separator Mat	erial	No	m. Thickne	ss Nom. Diamet	er
	inyl Chloride	0.0	38 in (0.97 n	nm) 0.34 in (8.6 mi	m)

Electricals

Nom. Conductor DCR		Max. Current		
4.4	Ohm/1000ft	13 Amps per Conductor at 25°C		

Voltage



Mechanical Characteristics

Temperature

UL Temperature 60°C

Bend Radius

Standards and Compliance

Stationary Min. Installation Min.

Environmental Suitability:	Outdoor, Sunlight Resistance

NEC / UL Compliance:	Article 400, SJT
AWM Compliance:	SJT
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.484 Revision Date: 01-20-2023

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
19349 010250	Black	Reel	250 ft	612825126935
19349 008250	Gray	Reel	250 ft	612825126928

© 2023 Belden, Inc

All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.