




Wire Protection & Management > Cable Glands > EP-SIG-1SNG622



Cable Gland Product Type: **Cable Gland**
Cable Gland & Accessory Style: **Snap-In**
Primary Product Material: **PA6**
Clamping Diameter Range: **16. – 28. mm**
Primary Product Color: **Gray**

[All EP-SIG-1SNG622 \(36\)](#)

Features

Product Type Features

| | |
|-------------------------------|-------------|
| Cable Gland Product Type | Cable Gland |
| Cable Gland & Accessory Style | Snap-In |
| Sealable | Yes |

Body Features

| | |
|--------------------------|------|
| Primary Product Material | PA6 |
| Primary Product Color | Gray |

Dimensions

| | |
|-------------------------|--------------|
| Clamping Diameter Range | 16. – 28. mm |
| Thread Length | 13.2 mm |

Usage Conditions

| | |
|-----------------------------|---------------------------|
| Operating Temperature Range | -20 – 100 °C[-4 – 212 °F] |
|-----------------------------|---------------------------|

Industry Standards

| | |
|------------------------|----------|
| UL Flammability Rating | UL 94V-2 |
|------------------------|----------|



Packaging Features

| | |
|------------------|-----|
| Packaging Method | Bag |
|------------------|-----|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings
EP-SIG-SZ40-GR-A

English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNG622032R0000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNG622032R0000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNG622032R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Catalog - ENTRELEC Cable Glands

English