

product type designation

product description

IE TP Cord RJ45/RJ45, 4x2

Patch cable, preferred length, preassembled with two RJ45 connectors (10/100/1000/10000MB)

Industrial Ethernet TP Cord RJ45/RJ45, CAT 6A, TP cable 4x2, pre-assembled with 2 RJ45 connectors, length 50 m.



suitability for use

Easy connection of terminal devices to the IE FC cabling system

cable designation

LI 02YSCH 4x2x0,15 PIMF GN FRNC

wire length

50 m

electrical data

number of electrical connections

2

attenuation factor per length

- at 10 MHz / maximum 0.086 dB/m
- at 100 MHz / maximum 0.28 dB/m
- at 300 MHz / maximum 0.501 dB/m
- at 600 MHz / maximum 0.735 dB/m

impedance

- at 1 MHz ... 100 MHz 100 Ω
- at 10 MHz ... 600 MHz 100 Ω

relative symmetrical tolerance

- of the characteristic impedance at 1 MHz ... 100 MHz 15 %
- of the characteristic impedance at 10 MHz ... 600 MHz 10 %

transfer impedance per length / at 10 MHz

10 mΩ/m

loop resistance per length / maximum

290 mΩ/m

operating voltage

- RMS value 80 V

NVP value in percent

80 %

mechanical data

number of electrical cores

8

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tinned copper wires

core diameter

- of AWG26 insulated conductor 0.5 mm

outer diameter

- of inner conductor 0.5 mm
- of the wire insulation 1 mm
- of cable sheath 6.2 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.3 mm

material

- of the wire insulation polyethylene (PE)

<ul style="list-style-type: none"> of cable sheath 	FRNC
color	
<ul style="list-style-type: none"> of the insulation of data wires of cable sheath 	white/blue, white/orange, white/green, white/brown green
bending radius	
<ul style="list-style-type: none"> with single bend / minimum permissible with multiple bends / minimum permissible 	31 mm 43.5 mm
weight per length	50 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport during installation note 	-25 ... +80 °C -25 ... +80 °C -25 ... +80 °C -25 ... +80 °C In fixed installation -40 °C to 80 °C
fire behavior	flame resistant according to IEC 60332-1-2, smoke density according to IEC 61034
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
<ul style="list-style-type: none"> to mineral oil to grease 	oil resistant according to IEC 60811-2-1 (4 h / 70°C) Conditional resistance
radiological resistance / to UV radiation	not resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free silicon-free 	Yes Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	Yes; E130266 AWM STYLE 21279
certificate of suitability	
<ul style="list-style-type: none"> EAC approval UL approval RoHS conformity 	Yes Yes Yes
standard for structured cabling	Cat6A
Marine classification association	
<ul style="list-style-type: none"> American Bureau of Shipping Europe Ltd. (ABS) French marine classification society (BV) Det Norske Veritas (DNV) Germanische Lloyd (GL) Lloyds Register of Shipping (LRS) Nippon Kaiji Kyokai (NK) Polski Rejestr Statkow (PRS) 	No No No No No No No
reference code	
<ul style="list-style-type: none"> according to IEC 81346-2 according to IEC 81346-2:2019 	WG WGB
further information / internet-Links	
Internet-Link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool to website: Industrial communication to website: Industry Mall to website: Information and Download Center to website: Selection guide for cables and connectors to website: Image database to website: CAx-Download-Manager to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
last modified:	6/25/2022 