



Product: [76401TS](#)

MachFlex™, 2 C #28 Str TC, SRPVC Ins, OS+TC Brd, PVC Jkt, CMG

[Request Sample](#)

Product Description

MachFlex™ for High Flex, 2 Conductor 28AWG (7x36) Tinned Copper, SRPVC Insulation, Overall Beldfoil®+Tinned Copper Braid(85%) Shield, PVC Outer Jacket, CMG

Technical Specifications

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	1	28 AWG	7x36	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.010 in (0.25 mm)	0.035 in (0.89 mm)	Black and Red

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	26 AWG (7x34) TC
Braid	Tinned Copper (TC)	85%	

Outer Jacket

Separator	Material	Nom. Thickness	Nom. Diameter
Paper Tape	PVC - Polyvinyl Chloride	0.040 in (1.0 mm)	0.186 in

Overall Cable Diameter (Nominal): 0.186 in

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Inductance Cond-Grnd	Max. Current
Pair(s)	65 Ohm/1000ft	27 pF/ft (89 pF/m)	49 pF/ft (160 pF/m)	70 Ohm	0.22 µH/ft	1.3 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-10°C To 105°C (Static), 5°C To 105°C (Dynamic)

Bend Radius

Stationary Min.	Installation Min.
1.86 in (47.2 mm)	1.86 in

Max. Pull Tension: 7.6 lbs (3.4 kg)

Bulk Cable Weight:	22 lbs/1000ft
--------------------	---------------

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL1685 UL Loading
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2661, AWM 10002, AWM I/II A/B
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.144 Revision Date: 05-05-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	UPC
76401TS 008100	Gray	Reel	612825411154
76401TS 0081000	Gray	Reel	612825411161

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.