

## Specification Sheet

Part Number: 156-00799



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

Two piece assembly allows the mount to slide along the strap ensuring proper orientation.

2-Piece Cable Tie & Edge Clip, 5.8" Long, EC20, 3-6mm Panel, 30lb, PA66HS/PA66HIRHS, Black, 500/pkg

|                |           |
|----------------|-----------|
| Article Number | 156-00799 |
|----------------|-----------|

|      |          |
|------|----------|
| Type | T30REC20 |
|------|----------|

|       |            |
|-------|------------|
| Color | Black (BK) |
|-------|------------|

|              |     |
|--------------|-----|
| Quantity Per | bag |
|--------------|-----|

|                     |                                                                                                                                                                                                                                                                                                                                     |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | This cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing. |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                                                     |
|-------------------|-----------------------------------------------------------------------------------------------------|
| Short Description | 2-Piece Cable Tie & Edge Clip, 5.8" Long, EC20, 3-6mm Panel, 30lb, PA66HS/PA66HIRHS, Black, 500/pkg |
|-------------------|-----------------------------------------------------------------------------------------------------|

|                  |                              |
|------------------|------------------------------|
| Global Part Name | T30REC20-PA66HS/PA66HIRHS-BK |
|------------------|------------------------------|

|                                     |      |
|-------------------------------------|------|
| Minimum Tensile Strength (Imperial) | 30.0 |
|-------------------------------------|------|

|                                   |     |
|-----------------------------------|-----|
| Minimum Tensile Strength (Metric) | 135 |
|-----------------------------------|-----|

|                     |     |
|---------------------|-----|
| Length L (Imperial) | 6.0 |
|---------------------|-----|

|                   |       |
|-------------------|-------|
| Length L (Metric) | 150.0 |
|-------------------|-------|

|                 |                                   |
|-----------------|-----------------------------------|
| Fixation Method | EdgeClip, top, assembled, 2 piece |
|-----------------|-----------------------------------|

|                               |      |
|-------------------------------|------|
| Identification Plate Position | none |
|-------------------------------|------|

|         |                 |
|---------|-----------------|
| Variant | Inside Serrated |
|---------|-----------------|

|                    |      |
|--------------------|------|
| Width W (Imperial) | 0.14 |
|--------------------|------|

|                  |     |
|------------------|-----|
| Width W (Metric) | 3.6 |
|------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Min (Imperial) | 0.20 |
|--------------------------------|------|

|                              |     |
|------------------------------|-----|
| Bundle Diameter Min (Metric) | 1.0 |
|------------------------------|-----|

|                                |     |
|--------------------------------|-----|
| Bundle Diameter Max (Imperial) | 1.4 |
|--------------------------------|-----|

|                              |      |
|------------------------------|------|
| Bundle Diameter Max (Metric) | 32.0 |
|------------------------------|------|

|                        |      |
|------------------------|------|
| Thickness T (Imperial) | 0.04 |
|------------------------|------|

|                     |      |
|---------------------|------|
| Height H (Imperial) | 0.04 |
|---------------------|------|

|                                |                                                                                                         |
|--------------------------------|---------------------------------------------------------------------------------------------------------|
| Height H (Metric)              | 1.1                                                                                                     |
| Panel Thickness Min (Imperial) | 0.12                                                                                                    |
| Panel Thickness Max (Imperial) | 0.24                                                                                                    |
| Panel Thickness Min (Metric)   | 3.00                                                                                                    |
| Panel Thickness Max (Metric)   | 6.00                                                                                                    |
| Material                       | Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| Material Shortcut              | PA66HIRHS PA66HS                                                                                        |
| UV Resistant (Yes/No)          | No                                                                                                      |
| Reach Compliant (Article 33)   | No                                                                                                      |
| ROHS Compliant                 | Yes                                                                                                     |
| Package Quantity (Imperial)    | 500                                                                                                     |
| Package Quantity (Metric)      | 500                                                                                                     |
| Customs Number                 | 3926909988                                                                                              |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)