

FOC-OP12-OP12-GL02/10 - Connecting cable



1415353

<https://www.phoenixcontact.com/us/products/1415353>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 12



Product description

Robust connecting cable Q-ODC-12 to Q-ODC-12, push-pull interlocking, degree of protection: IP68

Your advantages

- Compact design with MT ferrule
- Push-pull interlocking
- For extreme ambient conditions

Commercial data

Item number	1415353
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNHAA
Catalog page	Page 390 (C-2-2019)
GTIN	4055626047898
Weight per piece (including packing)	685 g
Weight per piece (excluding packing)	615 g
Customs tariff number	85447000
Country of origin	PL

FOC-OP12-OP12-GL02/10 - Connecting cable

1415353

<https://www.phoenixcontact.com/us/products/1415353>



Technical data

Product properties

Product type	Data cable preassembled
Sensor type	Ethernet
Number of positions	12

Electrical properties

Attenuation	typ. 0.15 dB
	max. 0.35 dB
Transmission medium	Multi-mode fiberglass

Mechanical properties

Tensile strength short-term/long-term	500 N
---------------------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Outer sheath, material	LSFH

Connector

Connection 1

Handle color	black
Insertion/withdrawal cycles	500 (In the event of repeated cleaning)
Degree of protection	IP68 (IEC 60529)
	IP68
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)
Number of positions	12
Insertion/withdrawal cycles	500
Locking type	Push Pull

Connection 2

Handle color	black
Insertion/withdrawal cycles	500 (In the event of repeated cleaning)
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)
Number of positions	12
Degree of protection	IP68 (IEC 60529)
Locking type	Push Pull

Cable/line

Cable length	10 m
Cable weight	55.00 kg/km
Cable type	Multimode fiberglass
Cable type	Zip cord, fiberglass
Cable abbreviation	12.../H(ZNG)H-...70

FOC-OP12-OP12-GL02/10 - Connecting cable

1415353

<https://www.phoenixcontact.com/us/products/1415353>



External cable diameter	7 mm
Outer sheath, material	LSFH
External sheath, color	black
Wire diameter incl. insulation	250 µm
Individual wire diameter	250 µm
Smallest bending radius, fixed installation	≥ 70 mm
Tensile strength short-term/long-term	500 N
Lateral pressure short term	500.00 N/cm
Lateral pressure, long-term	200.00 N/cm
Halogen-free	complying with IEC 60754-1/2

FO cable

Number of fibers	12
Fiber	62.5/125 µm OM1
Fiber type	Multimode fiberglass 62.5/125 µm
Attenuation	typ. 0.35 dB
Transmission medium	Multi-mode fiberglass

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)
Shock	50g, in accordance with IEC 61300-2-9

FOC-OP12-OP12-GL02/10 - Connecting cable

1415353

<https://www.phoenixcontact.com/us/products/1415353>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1415353>



EAC

Approval ID: 19060508

Classifications

ECLASS

ECLASS-11.0	27440312
ECLASS-12.0	27440312
ECLASS-13.0	27440312

ETIM

ETIM 8.0	EC002641
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FOC-OP12-OP12-GL02/10 - Connecting cable

1415353

<https://www.phoenixcontact.com/us/products/1415353>



Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	---

FOC-OP12-OP12-GL02/10 - Connecting cable



1415353

<https://www.phoenixcontact.com/us/products/1415353>

Accessories

FOC-MODUL:3U-OS12-LCD6-OM1 - Module

1419978

<https://www.phoenixcontact.com/us/products/1419978>

1*12-insert 3U module, type: 19"-rack mount patch module, degree of protection: IP20, number of positions: 1*12, marking material: aluminum, color: gray



Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com