

Ratings

Voltage: 300 V
 Temperature: -25 to 80 °C
 Flammability: VW-1

Conductor

Conductor count: 6
 Gauge: 18 AWG 0.82 mm²
 Material: tinned copper strands
 Strand size: $\varnothing 0.16$ mm x 41
 Resistance at 20 °C: 23.2 Ω /km max

Insulator

Material: PVC
 Color: red, black, white, yellow, blue, green
 Diameter: $\varnothing 1.8 \pm 0.10$ mm
 Nominal thickness: 0.29 mm
 Resistance at 20 °C: 10 M Ω /km min



Outer jacket

Material: PVC
 Color: white
 Diameter: $\varnothing 7.1 \pm 0.30$ mm
 Nominal thickness: 0.85 mm

Wire marking: E339579 UL AWM STYLE 2464 18 AWG 80°C
 300V VW-1 --- cUL AWM I/II A 80°C 300V FT1 TENSILITY

Tests

Insulation tensile strength: 2.11 kgf/mm²
 Jacket tensile strength: 1.05 kgf/mm²
 After aging at 113 ± 2 °C for 7 days:
 Minimum tensile strength 70 % original
 Minimum elongation 65 % original
 Heat shock: 121 ± 1 °C /1 hour, no observed degradation
 Deformation: 121 ± 1 °C /1 hour, ≤ 50 %
 Cold bend: -10 ± 2 °C /1 hour, no observed cracking



Revision:	Date:	Description:	Prepared:	Notes:	TENSILITY tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com
A	5/15/2019	Initial release	Verified:	RoHS compliant Function test: no open, no short circuit, no intermittent	
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Description:	Size: Part number:
				Wire, 6C TS, 18 AWG, UL2464, 300V, 80C, 7.1 mm, VW-1, PVC, 60P, white	A 30-01287
				Scale: 8:1	Sheet 1 of 1

5

↑

4

3

2

1