

RF Cable Assembly

SF526V/35VF/35VM/38in **Item: 85070046**

Description

SUCOFLEX 526V microwave cable assemblies set a new measurement standard for vector network analyzers (VNAs) through 26.5 GHz.



Product Configuration

Cable	SUCOFLEX 526V		
Type Description Connector A	35VF (PORT)		
Series Connector A	3.5mm	jack	straight
Type Description Connector B	35VM (DUT)		
Series Connector B	3.5mm	plug	straight
Length	965 mm REF to REF		
	38 inches		

Technical Data

Electrical Data			
Impedance	50 Ω		
Operating Frequency (max.)	26.5 GHz		
Return Loss (min.)	-20 dB	VSWR : 1.222	
Insertion Loss (max)	3.6 dB		
Signal delay	4.17 ns/m		
Velocity of propagation	80 %		
Screening effectiveness	≥ 90 dB up to 26.5 GHz		
Phase stability vs. temperature	50 ppm	15 °C to 30 °C at 26.5 GHz	
Amplitude stability vs. Flexure (max)	±0.04 dB		
Phase stability vs. Flexure (max)	0.28 ° / GHz		
Mechanical Data			
Diameter cable	13 mm		
Bending radius static (min.)	50 mm		
Flex Life (cycles)	100000		
Weight	0.35 kg		
Environmental Data			
Operating temperature	15 °C to + 30 °C	(Laboratory conditions, analyzer specific)	
2011/65/EU (RoHS)	compliant		
2012/19/EU (WEEE)	relevant		
2006/1907/EC (REACH)	compliant		