



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M8 MS - M12 FS CABLE ASSY BL



M8/M12 Application Type: **Sensor/Actuator**

Number of Positions: **4**

Connector & Keying Code: **A**

Connector Type (End A): **M8 Plug**

Connector Type (End B): **M12 Socket**

[All M8 MS - M12 FS CABLE ASSY BL \(19\)](#)

Features

Product Type Features

|                        |            |
|------------------------|------------|
| Connector Type (End A) | M8 Plug    |
| Connector Type (End B) | M12 Socket |
| Cable Assembly Type    | M8 to M12  |

Configuration Features

|                     |   |
|---------------------|---|
| Number of Positions | 4 |
|---------------------|---|

Electrical Characteristics

|                   |        |
|-------------------|--------|
| Operating Voltage | 34 VAC |
|-------------------|--------|

Body Features

|                         |                           |
|-------------------------|---------------------------|
| Cable Color             | Black                     |
| Connector Color (End B) | Black                     |
| Connector Color (End A) | Black                     |
| Jacket Material         | PUR                       |
| Wire Color (Base)       | Brown, White, Blue, Black |
| Connector & Keying Code | A                         |

Contact Features

|                              |     |
|------------------------------|-----|
| Contact Current Rating (Max) | 4 A |
|------------------------------|-----|

Mechanical Attachment



|                               |          |
|-------------------------------|----------|
| Thread Size                   | M8 x M12 |
| Connector Orientation (End A) | Straight |
| Connector Orientation (End B) | Straight |

Housing Features

|                  |         |
|------------------|---------|
| Housing Material | Plastic |
|------------------|---------|

Dimensions

|                        |                 |
|------------------------|-----------------|
| Outside Cable Diameter | 4.4 mm[.173 in] |
| Wire Size              | .326 mm²        |

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -40 – 80 °C[-40 – 176 °F] |
|-----------------------------|---------------------------|

Operation/Application

|                         |                 |
|-------------------------|-----------------|
| M8/M12 Application Type | Sensor/Actuator |
| Shielded                | No              |

Packaging Features

|                  |     |
|------------------|-----|
| Packaging Method | Box |
|------------------|-----|

Other

|                              |              |
|------------------------------|--------------|
| Field Serviceable            | Yes          |
| Cable Assembly Length        | 2 m          |
| Cable Assembly Configuration | Double Ended |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JAN 2022 (223)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                            |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                   |



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T4051320004-004

M8 CABLE ST FEMALE 3M 4P PUR CABLE

Customers Also Bought



TE Part #T4110002051-000

M12,FEMALE,STRAIGHT,A CODE,5P, PG9,GOLD



TE Part #T4011008041-000

M8,SCREW, MALE,S,UNSHIELD,4P, GOLD



TE Part #1-2273109-5

M8 strgt plug to M12 strgt socket AA



TE Part #T4073014041-001

M8.FMLE.PNLFRONT.4POS.STR WIRE



TE Part #TAA755A5501-040

M12A5-MS-FS-PUR-4.0M



TE Part #284051-3

TERMI-BLOK VERTICAL PLUG STACK



TE Part #2329362-1

PB OFF/ON RC BLK M1 TERM IP68 500MM LHS



TE Part #SG1-80-2

STRING POT, 80 INCH RANGE

Documents

Product Drawings

M8 strgt plug to M12 strgt socket AA

English



CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2273109-5\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2273109-5\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2273109-5\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

M8 / M12 Connector System Catalog

Japanese

Product Specifications

Product Specification

English