


SURFACE MOUNT GLASS PASSIVATED BRIDGE RECTIFIERS		REVERSE VOLTAGE - 50 to 1000Volts FORWARD CURRENT - 3.0 Amperes							
FEATURES ●Rating to 1000V PRV ●Ideal for printed circuit board ●Low forward voltage drop,high current capability ●Reliable low cost construction utilizing molded plastic technique results in inexpensive product ●Lead tin Pb/Sn copper ●The plastic material has UL flammability classification 94V-0 MECHANICAL DATA ●Polarit: As marked on Body ●Weight: 0.02 ounces,0.38 gras ●Mounting position: Any		 DB Dimensions in inches and (millimeters)							
MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS									
Rating at 25°C ambient temperature unless otherwise specified.									
Single phase, half wave ,60Hz, resistive or inductive load.									
For capacitive load, derate current by 20%									
CHARACTERISTICS	SYMBOL	DB301	DB302	DB303	DB304	DB305	DB306	DB310	UNIT
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current @T _A =40°C	I _(AV)	3.0							A
Peak Forward Surage Current 8.3ms Single Half Sine-Wave Super Imposed on Rated Load (JEDEC .Method)	I _{FSM}	90							A
Maximum Forward Voltage at 2.0A DC	V _F	1.1							V
Maximum DC Reverse Current @T _J =25°C at Rated DC Blocking Voltage @T _J =125°C	I _R	10 500							uA
I ² t Rating for Fusing (t<8.3ms)	I ² t	10.4							A ² s
Typical Junction capacitance Per Element(Note1)	C _J	25							pF
Typical Thermal Resistance (Note2)	R _{θJC}	40							°C/W
Operating Temperature Range	T _J	-55 to +150							°C
Storage Temperature Range	T _{STG}	-55 to +150							°C
Note:1.Measured at 1.0MHz and applied reverse voltage of 4.0V DC									
2.Thermal resistance from junction to ambient mounted on P.C.B with 0.5*0.5"(13*13mm) copper pads.									

FIG.1-DERATING CURVE FOR
OUTPUT RECTIFIED CURRENT




FIG.2-MAXIMUM NON-REPETITIVE PEAK
FORWARD SURGE CURRENT




FIG.3-TYPICAL JUNCTION CAPACITANCE




FIG.4-TYPICAL FORWARD CHARACTERISTICS




FIG.5-TYPICAL REVERSE CHARACTERISTICS

