



Terminals & Splices > Splices



Sealable: **Yes**

Compatible Insulation Diameter Range: **2.03 mm [.08 in]**

Primary Product Color: **Black**

Product Length: **25.4 mm [1 in]**

Government Qualified Splice: **No**

Features

Product Type Features

Sealable	Yes
----------	-----

Body Features

Insulation Material	Heat Shrinkable, Crosslinked, Flame-Retardant Modified Polyolefin
Primary Product Color	Black

Dimensions

Compatible Insulation Diameter Range	2.03 mm[.08 in]
Product Length	25.4 mm[1 in]

Usage Conditions

Insulation Option	Fully Insulated
-------------------	-----------------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)




Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #YDTS20W19-35PNV001
RECP ASSY




TE Part #450213-000
CTA-0165




TE Part #YDL64H-12-12PNV001
HERM RECP




TE Part #180481-000
MTCP-116-05S1




TE Part #50832-3
TERMINAL,PIDG PTFE R 22-20 10




TE Part #ZPF000000000007847
983-0YE 08-03 PN



TE Part #148032-000
MTCST-YH1-P03



TE Part #RSM04-12-14P
RECP ASSY



Documents

Product Drawings

D-300-01

English

Datasheets & Catalog Pages

1654025_Sec3_TC_Caps

English

Raychem Electrical Interconnect Products

English