



**Product:** [9402](#)

Audio, Control & Instrument, #20-2pr, SR-PVC, Individ. Foil, PVC Jkt, CMG

**Product Description**

Audio, Control & Instrument Cable, 2 Pair, 20 AWG stranded (7x28) tinned copper conductors, semi-rigid PVC insulation, individually shielded pairs with Beldfoil® (100% coverage), 22 AWG stranded tinned copper drain wire, overall PVC jacket.

**Technical Specifications**

**Product Overview**

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------

**Construction Details**

**Conductor**

Element	No. of Elements	Size	Stranding	Material
Pair(s)	2	20 AWG	7x28	TC - Tinned Copper

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.011 in (0.28 mm)	0.058 in (1.5 mm)	Red & Black, Green & White

**Inner Shield**

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (19x34) TC	each pair

**Outer Jacket**

Separator	Material	Nom. Thickness	Nom. Diameter
Polyester Tape	PVC - Polyvinyl Chloride	0.041 in (1.0 mm)	0.300 in (7.62 mm)

Overall Cable Diameter (Nominal):	0.300 in (7.62 mm)
-----------------------------------	--------------------

**Electrical Characteristics**

**Electricals**

Element	Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Pair(s)	11.3 Ohm/1000ft	11.54 Ohm/1000ft (37.86 Ohm/km)	55 pF/ft (180 pF/m)	95 pF/ft (310 pF/m)	3.8 Amps per Conductor at 25°C

**Voltage**

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2464)

**Mechanical Characteristics**

**Temperature**

UL Temperature	Operating
80°C	-20°C to +80°C

**Bend Radius**

Stationary Min.	Installation Min.
3.0 in (76 mm)	3.0 in (76 mm)

Max. Pull Tension:	60 lbs (27 kg)
Bulk Cable Weight:	49 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

History

Update and Revision:	Revision Number: 0.545 Revision Date: 04-19-2023
----------------------	--------------------------------------------------

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
9402.00305	Chrome	Reel	305 m	8719605020512	
9402 060U500	Chrome	UnReel	500 ft	612825239987	
9402 0601000	Chrome	Reel	1,000 ft	612825239994	C
9402 0605000	Chrome	Reel	5,000 ft	612825240006	

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.