

APPROVAL SHEET

Customer Name :

Customer P/N :

Frequency : 13.560000 MHz

Aker Approved P/N: CXAN-013560-5-AL-00

Aker MPN : CXAN-013560-5-AL-00

Rev. : 1

ISSUE DATE : Sep.27.2022

APPROVED	CHECKED	PREPARED
		PTY
APPROVED BY CUSTOMER		

AKER TECHNOLOGY CO., LTD.

ADDRESS : NO 11-3, Jianguo Rd., Tanzi Dist., Taichung City 427, Taiwan.

TEL : 886-4-25335978 FAX : 886-4-25336011

Web: www.aker.com.tw

MSL:Level 1

RoHS compliant



Aker Approved P/N :		CXAN-013560-5-AL-00	
APPROVED	:	Tin	SHEET : 1 of 9
PREPARED	:	piy	REV. : 1



Aker Approved P/N :	CXAN-013560-5-AL-00		
APPROVED :	Tin	SHEET :	2 of 9
PREPARED :	piy	REV . :	1
Confidential			

SMD CRYSTAL SPECIFICATION

1 . ELECTRICAL CHARACTERISTICS

■ Standard atmospheric conditions

Unless otherwise specified , the standard range of atmospheric conditions for making measurement and tests are as follow :

Ambient temperature : 25 ± 5 °C

Relative humidity : 40%~70%

If there is any doubt about the results , measurement shall be made within the following limits :

Ambient temperature : 25 ± 3 °C


Relative humidity : 40%~70%

- AKER Model : CXAN-531
- Oscillation Mode : Fundamental
- Cutting Mode : AT CUT
- Measurement Equipment : 250B(Measured FL)
- Insulation Resistance : More than 500M ohms at DC 100V

Parameters	Symbol	Electrical Spec				Notes
		Min.	Typ.	Max.	Units.	
Nominal Frequency	FL	13.560000			MHz	
Frequency Tolerance		± 10		ppm	at $25^\circ\text{C} \pm 3^\circ\text{C}$	
Frequency Stability		± 30		ppm	Operating Temp (Refer 25°C)	
Load Capacitance	CL	12			pF	
Aging		± 3			ppm	First Year
Operating Temperature		-40	~	85	°C	
Storage Temperature Range		-55	~	125	°C	
Drive Level	DL			100	uW	
Equivalent Series Resistance	ESR			50	Ω	@Series
Shunt Capacitance	C0			7	pF	


Please kindly be noted that AKER DO NOT guarantee parts quality which involves human security application.

2. MARKING :




3. DIMENSION :

(Unit : mm)



4 . STRUCTURE ILLUSTRATION




COMPONENTS		MATERIALS	COMPONENTS		MATERIALS
A	Base (Package)	Ceramic(Al ₂ O ₃)+Kovar(Fe/Co/Ni)	D	Electrode	Cr / Ag
B	Conductive adhesive	Ag / Silicon resin	E	Lid	Fe/Co/Ni
C	Crystal blank	SiO ₂			

5 . PACKING :


TAPE SPECIFICATION

(Unit : mm)




OUTLINE DIMENSION

(Unit : mm)




6. COVER TAPE ADHESION STRENGTH :




*** In the case, the cover tape is pulled off under the above conditions, the cover tape adhesion strength should be 10.2g~71.4g
Plastic tape: 10.2g~71.4g

(Cover tape adhesion strength)


7. SOLDERING REFLOW PROFILE



8. PACKING :



BOX = 1000 PCS / REEL



SMD product packs 32 BOX = The outside box packs (1000 PCS * 32 BOX = 32000 PCS)(MAX)



Aker Approved P/N :	CXAN-013560-5-AL-00		
APPROVED :	Tin	SHEET :	8 of 9
PREPARED :	piy	REV. :	1
Confidential			

9. MECHANICAL PERFORMANCE

TEST ITEMS	TEST METHODS AND TEST CONDITION	PERFORMANCE
9.1 Drop Test	<p>The specimen is measured for its frequency and resistance before the test. It is then dropped from a height of 75 cm or more as a free fall object onto a hard wooden plate of 30mm or more in thickness.</p> <p>(in accordance with JIS-C0044)</p>	
9.2 Vibration Test	<p>The specimen is measured for its frequency and resistance before the test. Most them into X,Y and Z axes, respectively, for the vibration test.</p> <p>Vibration condition:</p> <p>Frequency range ; 20 ~ 2000HZ</p> <p>Peak to peak amplitude : 1.52 mm</p> <p>Peak acceleration : 20G</p> <p>Sweep time : 20 minute / axis</p> <p>Pendicular total test time : 4 hours</p> <p>(in accordance with MIL-STD-883F : 2007.3)</p>	To satisfy the electrical performance .
9.3 Resistance to Soldering Test	<p>The specimen is measured for its frequency and resistance before the test. Place the specimen on the belt of the converynace and let it pass through the reflow with the presetted temperature condition.</p> <p>After passing twice the reflow place, the specimen under the referee condition for ~2 hours and then measure its electrical performance.</p> <p>Temperature Condition of IR Simulation:</p> <p>The temperature range of the preheated section is setted at 150 ~ 180°C for 60~120 sec. For the next section the temperature range is setted at 217~260°C for 45~90 sec. and within this time range the specimen should be able to sustain at the peak temperature, 260+/-3°C , for 10 sec long.</p> <p>(in accordance with JESD22-B106-B)</p>	
9.4 Fine Leak Test	<p>Place the specimen in a pressurized container and pressurize it with the detection gas (mixed gas consisting of 95% or more helium) for at least 2 hours.</p> <p>Complete the measurement of the concentration of helium within 30 min after taking it out from the pressurized container.</p> <p>(in accordance with MIL-STD-883F : 1014.11)</p>	Less than 1.0 * 10 ⁻⁸ atm .c.c. / sec, Helium
	<p>The referee condition .</p> <p>Temperature 25 ± 2 °C</p> <p>Humidity 44 ~ 55 %</p> <p>Pressure 86 ~ 106 kPa</p> <p>(in accordance with MIL-STD-883E : 1014. 9)</p>	



Aker Approved P/N :	CXAN-013560-5-AL-00	
APPROVED :	Tin	SHEET : 9 of 9
PREPARED :	piy	REV. : 1
Confidential		

10 . CLIMATIC RESISTANCE

TEST ITEMS	TEST METHODS AND TEST CONDITION	PERFORMANCE
10.1 Low Temp Exposure Test	<p>The specimen is measured for its frequency and resistance before the test .</p> <p>Place the specimen in the chamber and kept it at the temperature of $-40 \pm 3^\circ\text{C}$ for 168 ± 6 hours .</p> <p>Take the specimen out of the chamber and measure its electrical performance after leaving $1 \sim 2$ hours under the referee condition .</p> <p>(in accordance with JIS-C0020)</p>	
10.2 Aging Test	<p>The specimen is measured for its frequency and resistance before the test .</p> <p>Place the specimen in the testing chamber and keep it at the temperature of $+125 \pm 3^\circ\text{C}$ for 720 ± 48 hours .</p> <p>And then take the specimen out of the chamber and measure its electrical performance after leaving for $1 \sim 2$ hours under the referee condition .</p> <p>(in accordance with JIS-C0021)</p>	To satisfy the electrical performance .
10.3 High Temperature & High Humidity	<p>The specimen is measured for its frequency and resistance before the test .</p> <p>Place the specimen in the testing chamber and kept it at the temperature of $+85 \pm 5^\circ\text{C}$ and humidity of $85 \pm 5\%$ for 168 ± 6 hours . and then take the specimen out and measure its electrical performance after leaving for $1 \sim 2$ hours under the referee condition .</p> <p>(in accordance with MIL-STD-883F : 1004.7)</p>	
10.4 Temperature Cycle Test	<p>The specimen is measured for its frequency and resistance before the test .</p> <p>Subject the specimen to the 100 cycles of temperature ranges stated below .</p> <p>High temp . $+125 \pm 3^\circ\text{C}$ (15 ± 3 min).</p> <p>Low temp . $-55 \pm 3^\circ\text{C}$ (15 ± 3 min).</p> <p>Measure its electrical performance after leaving it for $1 \sim 2$ hours under the referee condition .</p> <p>(in accordance with MIL-STD-883F : 1010.8)</p>	