




技术要求:

- 1、塑件材料: PA66 (UL-94V-0)
- 2、接触件: 黄铜镀锡
- 3、接触电阻: $\leq 10\text{m}\Omega$
- 4、绝缘电阻: $\geq 1000\text{M}\Omega$
- 5、额定电压: 250V AC DC
- 6、额定电流: 2.0A AC DC
- 7、耐压: 能承受1000V AC/Minute
- 8、工作温度: $-25^{\circ}\sim +85^{\circ}$
- 9、可焊性试验: 浸锡面积 $\geq 95\%$ 温度 235^{+5}_{-0} , 时间 2.5 ± 0.5 秒
- 10、铅和镉等六大有害物质含量要符合环保要求



Technical drawing of a rectangular plate with the following specifications:

- Overall width: $A + 0.20$
- Overall height: 2.00 ± 0.10
- Number of holes: 7
- Hole diameter: $\phi 0.90 \pm 0.10$
- Distance between the first and second hole from the left edge: 2.00 ± 0.10

SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

2	端子 Contact	黄铜	nx1	包铜(锡): 至少表面镀层30u"MIN, 其厚度 80u"MIN
1	基板 Wafer	PA66(UL94V-0)	1	白色
序号	名 称	材 料	数 量	附 注

GENERAL TOLERANCES			DRAWN BY	 Bossie (博锡)			
0.X	±0.25	X.° ±3°	CHK. BY				
0.XX	±0.12						
0.XXX	±0.05	X.X° ±0.5°	APRV. BY				
UNIT	SIZE	SCALE		DRAWING NO.	SHEET	PROD. NAME	PH 2.0 弯针 9 P
MM	A4	1:1		1 OF 1	PART NO.	BX-PH2.0-9PWZ	
				TITLE			

日期