

Product: <u>8812</u> ☑



Speaker Cable, 2 Conductor 12 AWG BC, Unshielded, CM

Product Description

2 Conductor 12 AWG, stranded (19x25) bare copper conductors, PVC/Nylon insulation, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications: AUDITORIUM, STADIUM, RACE TRACK, CHURCH, TEMPLE, SYNAGOGUE, PLACE OF ASSEMBLY, CASINO, SOUND

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
12	19x25	BC - Bare Copper	2
Condu	ctor Count:	2	2

Insulation

Layer	Material	
1	PVC - Polyvinyl Chloride	
2	Nylon	

Outer Shield



Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.37 in

Construction and Dimensions

Cabling



Electrical Characteristics

Conductor DCR



Voltage



Temperature Range

Operating Temperature Range:

-30°C To +75°C Wet; -30°C To +90°C Dry

Wet Temp Range:	-30°C To +75 °C
Dry Temp Range:	-30°C To +90°C Dry

Mechanical Characteristics

Bulk Cable Weight:	75 lbs/1000ft
Max. Pull Tension:	152 lbs
Min. Bend Radius/Minor Axis:	3.75 in

Standards

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2002/96/EC (WEEE)

Suitability

Suitability - Burial:	Yes			
Suitability - Indoor:	Yes			
Suitability - Outdoor:	Yes			
Suitability - Sunlight Resistance:	Yes			

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1581 Vertical Tray
CSA Flammability:	FT4
IEEE Flammability:	1202
UL voltage rating:	600 V RMS

Plenum/Non-Plenum

Diamona (MAI)	N-
Plenum (Y/N):	No

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
8812 0101000	Black	Reel	1,000 ft	612825216858
Footnote:			C - CRATI	E REEL PUT-UP.

History

Update and Revision:	Revision Number: 0.322 Revision Date: 04-14-2023	

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.