






RoHS

REV.	EC#	DESCRIPTION	DATE	DRAWING	CHECKED	APPROVED



RECOMMENDED PCB LAYOUT  
 ■ PATTERN PROHIBITION AREA



SIM pin assignment	
PIN#	Name
C1	VCC供电电压
C2	RST重置
C3	CLK时钟
C5	GND接地
C6	VPP程序电压
C7	I/O输入输出

- NOTES:
- MATERIAL:
    - Insulator: High Temperature Thermoplastic, UL94V-0; Color Black.
    - Terminal: Copper Alloy.
    - Shell: Stainless Steel.
  - PLATING:
    - Contact: Plated 50u" Ni Overall Contact Au 1u",
    - Shell: Plated 50u" Ni Overall, PAD Au 1u"
  - SPECIALITY:
    - Current Rating :0.5mA AC/DC max.
    - Voltage Rating :125V AC/DC
    - Ambient Temperature Range :-20° C~+60° C
    - Storage Temperature Range :-40° C~+70° C
    - Ambient Humidity Range :95% R.H. Max.
    - Contact Resistance:100mΩ max.
    - Insulation Resistance:1000MΩ min./500VDC
    - Mating Cycles:10,000 Insertions
    - Reflow peak temp.: 260° C ±5° C, 3~5 S
    - Mating Cycles:3,000 Insertions Min
  - PLEASE CONTACT I/Q SALES REPRESENTATIVE TO VERIFY PRODUCT DETAILS & AVAILABILITY

Unless otherwise specified tolerances are								
X.X	±0.30					DRAW NO.	DATE	DRAW NAME:
X.XX	±0.20	DWN		拔插式 NanoSIM卡卡座				
X.XXX	±0.10	CHK		P/N :				
X'	±3.0'	APVD						
X.X'	±1.5'							
 Third Angle Project		FINISH		UNIT	SCALE	WEIGHT	REV	SHEET
		DWG NO.	BX-SMN-1.35HJ-C	mm	1:1		A0	1 OF 2