


TE Internal #: T4151420008-005

M12 Pigtail Cable Assembly, 8 Position, 5 m, Sensor/Actuator,
Code A, M12 Socket, Single Ended, GF Nylon[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M12 A-Code Pigtail, Female, R/A, Single Ended Cable



M8/M12 Application Type: Sensor/Actuator

Number of Positions: 8

Connector & Keying Code: A

Connector Type (End A): M12 Socket

Cable Assembly Type: M12 Pigtail

[All M12 A-Code Pigtail, Female, R/A, Single Ended Cable \(140\)](#)

Features

Product Type Features

Connector Type (End A)	M12 Socket
Cable Assembly Type	M12 Pigtail

Configuration Features

Number of Positions	8
---------------------	---

Electrical Characteristics

Operating Voltage	30 VAC
-------------------	--------

Body Features

Cable Color	Gray
Connector Color (End A)	Black
Jacket Material	PUR
Conductor Material	Copper Alloy
Connector & Keying Code	A

Mechanical Attachment

Thread Size

M12

Connector Orientation (End A)

Right Angle

Housing Features

Housing Material

GF Nylon

Operation/Application

M8/M12 Application Type

Sensor/Actuator

Shielded

No

Packaging Features

Packaging Method

Box

Other

Field Serviceable

Yes

Cable Assembly Length

5 m

Cable Assembly Configuration

Single Ended

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023
(235)Candidate List Declared Against: JUNE
2023 (235)SVHC > Threshold:
Pb (4% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900
ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous

materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # T4151220008-005
RPC-M12-MR-8CON-PUR-5.0




TE Part # 2273094-3
M12 x 1.0 angled plug pig A

Customers Also Bought



TE Part #5-747913-2
25 Rcpt Solder Cup, Gold Flash



TE Part #5-747912-2
25 Plug Solder Cup, Gold Flash

Documents

Product Drawings

[RPC-M12-FR-8CON-PUR-5.0](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_T4151420008-005_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T4151420008-005_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T4151420008-005_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M8 / M12 Connector System Catalog](#)

English

[M8 / M12 Connector System Catalog](#)

Japanese

[Product Specifications](#)

English

[Agency Approvals](#)

UL

English