





PIN No.	PIN NAME
C8	RESERVED
C7	I/O
C6	VPP
C5	GND
C4	RESERVED
C3	CLK
C2	RST
C1	VCC



- NOTES:
- ELECTRICAL CHARACTERISTICS:
 - CURRENT RATING: 0.5 Amp. MAX.
 - VOLTAGE: 100V DC. MAX.
 - LDV LEVEL CONTACT RESISTANCE: 100 mOhms MAX. INITIALLY.
 - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC MIN. FOR 1 MINUTE.
 - INSULATION RESISTANCE: (INITIAL) 1000MOhms MIN. (FINAL) 100MOhms MIN. BY APPLYING 500V DC ON MATED AND UNMATED CONNECTORS THROUGH MIL-STD-202, METHOD 302.
 - MECHANICAL CHARACTERISTICS:
 - DURABILITY: 5000 CYCLES.
 - OPERATING TEMP. RANGE: -25°C TO 85°C. (INCLUDING TERMINAL TEMP. RISE)
 - STORAGE TEMP.: -40°C TO 85°C.
 - DIMENSIONS MARKED ∇ ARE MAJOR CHECKED DIMENSIONS.
 - HARMFUL MATERIAL CONTROL PLEASE FOLLOW DDC NO. 'EPI12'.

Bossie (博锡)			
E	PRODUCT SPEC. MICRO SIM CARD		
TITLE:	自弹式 MicroSIM卡 卡座 6P		
PART NO.	BX-SIM-1.35H6PJ-Z		
FILE NAME:			
SCALE	1:1	UNIT:mm	A4 SHEET: 1 of 1

工程变更通知单号 ECN(DCN) NO.	版次 REV	日期 DATE	说明 DESCRIPTION	改变 CHANGE	承认 APPRO.	General X±0.50 .X±0.30 .XX±0.20	Angle X°±2° .X°±1° .XX°±0.5°	设计 DESIGN	校阅 CHECK	承认 APPRO.
						GENERAL TOLERANCE UNLESS OTHERWISE NOTED				