

CABLE-D-25SUB/M/OE/0,25/S/1,0M - Cable



2926519

<https://www.phoenixcontact.com/us/products/2926519>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled shielded round cable; connection 1: Single wires (25-position) (The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.); connection 2: D-SUB pin strip (1x 25-position); cable length: 1 m

Your advantages

- Individual wire marking: 1, 2, 3, 4, etc.
- Individual wires fitted with ferrules
- Connector in accordance with IEC 60807-2/DIN 41652
- 1:1 connection
- Open end at one end
- D-SUB socket or pin strip at one end
- Screw connection: 2 UNC 4-40 screws
- Shield connection: H05V-K 1 mm² cable, black, length: 0.5 m

Commercial data

Item number	2926519
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C421
Product key	CK2135
Catalog page	Page 576 (C-5-2019)
GTIN	4046356547017
Weight per piece (including packing)	192.86 g
Weight per piece (excluding packing)	192.86 g
Customs tariff number	85444290
Country of origin	DE

CABLE-D-25SUB/M/OE/0,25/S/1,0M - Cable

2926519

<https://www.phoenixcontact.com/us/products/2926519>



Technical data

Product properties

Product type	System cable
--------------	--------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation)
	-10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path)	≤ 2 A (Uncoiled, see derating)

Cable/line

Cable length	1 m
--------------	-----

25X0.25 [PVC]

UL AWM Style	2464/1061
Number of positions	25
Shielded	yes
Cable type	25X0.25 [PVC]
Conductor type	Assembled shielded round cable
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross section	25x 0.25 mm ²
Wire diameter incl. insulation	1.2 mm ±0.05 mm
External cable diameter	9.8 mm ±0.5 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Bare Cu litz wires
Cable resistance	≤ 80 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km (at 20 °C)
Smallest bending radius, fixed installation	82 mm
Smallest bending radius, movable installation	155 mm
Max. bending cycles	5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no

CABLE-D-25SUB/M/OE/0,25/S/1,0M - Cable

2926519

<https://www.phoenixcontact.com/us/products/2926519>



Flame resistance	IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable) UL VW-1 CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)

color code

D-SUB25 (1)	() = white
D-SUB25 (2)	() = brown
D-SUB25 (3)	() = green
D-SUB25 (4)	() = yellow
D-SUB25 (5)	() = gray
D-SUB25 (6)	() = pink
D-SUB25 (7)	() = blue
D-SUB25 (8)	() = red
D-SUB25 (9)	() = black
D-SUB25 (10)	() = violet
D-SUB25 (11)	() = gray-pink
D-SUB25 (12)	() = red-blue
D-SUB25 (13)	() = white-green
D-SUB25 (14)	() = brown-green
D-SUB25 (15)	() = white-yellow
D-SUB25 (16)	() = yellow-brown
D-SUB25 (17)	() = white-gray
D-SUB25 (18)	() = gray-brown
D-SUB25 (19)	() = white-pink
D-SUB25 (20)	() = pink-brown
D-SUB25 (21)	() = white-blue
D-SUB25 (22)	() = brown-blue
D-SUB25 (23)	() = white-red
D-SUB25 (24)	() = brown-red
D-SUB25 (25)	() = white-black

Connection data

Connection 1

Connection method	Single wires
Stripping length (Sheath)	≈  mm
Number of positions	25
Note	The wires are marked and fitted with ferrules. The braided shield is routed to a separate cable end.

Connection 2

Connection in acc. with standard	IEC 60807-2 DIN 41652
----------------------------------	--------------------------

CABLE-D-25SUB/M/OE/0,25/S/1,0M - Cable

2926519

<https://www.phoenixcontact.com/us/products/2926519>



Connection method	D-SUB pin strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	25
Tightening torque	0.2 Nm
Insertion/withdrawal cycles	> 200
Pitch	2.77 mm

Notes

General	No additional touch protection is required when using a SELV/PELV voltage (≤ 30 V AC or 60 V DC).
General	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

CABLE-D-25SUB/M/OE/0,25/S/1,0M - Cable



2926519

<https://www.phoenixcontact.com/us/products/2926519>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2926519>

CSA	Approval ID: 70002966	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
		125 V	1 A	-	-

cUL Recognized	Approval ID: FILE E 238705	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
		125 V	2 A	-	-

UL Recognized	Approval ID: FILE E 238705	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
		125 V	2 A	-	-

EAC	Approval ID: RU*-DE.HB*35.B00385
-----	----------------------------------

cULus Recognized

CABLE-D-25SUB/M/OE/0,25/S/1,0M - Cable

2926519

<https://www.phoenixcontact.com/us/products/2926519>



Classifications

ECLASS

ECLASS-11.0	27242220
ECLASS-12.0	27242220
ECLASS-13.0	27242220

ETIM

ETIM 8.0	EC000237
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

CABLE-D-25SUB/M/OE/0,25/S/1,0M - Cable

2926519

<https://www.phoenixcontact.com/us/products/2926519>



Environmental product compliance

REACH SVHC

Lead 7439-92-1

China RoHS

Environmentally Friendly Use Period = 50 years

For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com