



- 1、塑件材料: CM3004 (UL-94V-0)
- 2、接触件: 黄铜镀锡
- 3、接触电阻: $\leq 10\text{m}\Omega$
- 4、绝缘电阻: $\geq 1000\text{M}\Omega$
- 5、额定电压: 250V AC DC
- 6、额定电流: 2.0A AC DC
- 7、耐压: 能承受1000V AC/Minute
- 8、工作温度: $-25^{\circ}\sim +85^{\circ}$
- 9、可焊性试验: 浸锡面积 $\geq 95\%$ 温度 220_{-0}^{+5} , 时间 2.5 ± 0.5 秒
- 10、铅和铜等六大有害物质含量要符合环保要求



Circuits	Dimensions (mm)		
	A	B	C
02	2.00	6.10	2.50
03	4.00	8.00	2.50
04	6.00	10.00	3.50
05	8.00	12.00	5.50
06	10.00	14.00	7.50
07	12.00	16.00	9.50
08	14.00	18.00	11.5
09	16.00	20.00	13.5
10	18.00	22.00	15.5
11	20.00	24.00	15.5
12	22.00	26.00	15.5
13	24.00	28.00	15.5
14	26.00	30.00	15.5
15	28.00	32.00	15.5



2	端子 Contact	黄铜	n×1	电镀(镍): 最小表面厚度30μMIN, 厚度 80μMIN.
1	基板 Wafer	LCP (UL94V-0)	1	白色
序号	名 称	材 料	数 量	附 注

GENERAL TOLERANCES			DRAWN BY		
0.X ±0.25	X° ±3°	CHK. BY			
0.XX ±0.12		APRV. BY			
0.XXX ±0.05	X.X° ±0.5°			SHEET	PROD. NAME HY2.0 弯针 7P
UNIT	SIZE	SCALE		DRAWING NO.	1 OF 1
MM	A4	1:1			PART NO. BX-HY2.0-7PWZ
				TITLE	