




SIM pin assignment	
PIN#	Name
C1	VCC 供电电压
C2	RST 重置
C3	CLK 时钟
C5	GND 接地
C6	VPP 程序电压
C7	I/O 输入输出



PCB 焊盘区
下沉避让区

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05



Specification

MATERIAL:

Insulator: High Temperature Thermoplastic, UL 94V-0.
Contact: Copper Alloy
SHELL: SUS

PLATING:

Contact: Plated 50u'' Ni Overall Contact Au 1U
Shell: Plated 50u'' Ni Overall
Plated 1u''Au Selective Contact Area

Electrical:

Current Rating :0.5mA AC/DC max.
Voltage Rating :125V AC/DC
Ambient Temperature Range :-20° C~+60° C
Storage Temperature Range :-40° C~+70° C
Ambient Humidity Range :95% R.H. Max.
Contact Resistance:100m Ω
Insulation Resistance:1000M min./500VDC
产品耐温温度: 260
Mating Cycles:3000Min Insertions

JB Bossie (博锡)

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY :	DATE :	PART NAME: 自弹式 MicroSIM 卡卡座 7P
	CHECKED BY:	DATE :	PART NO. BX-SIM-1.35H7PJ
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY:	DATE :	MOLD NO.
			DRAW NO.
			SHEET NO. 1 OF 1