

EL8095-000

✓ ACTIVE

D-CT

TE Internal #: EL8095-000

Printable Tubing, Continuous, Fluid Resistant, 3:1 Shrink Ratio,
Yellow, .375in [9.5mm] Expanded Inside Diameter, D-CT[View on TE.com >](#)

Identification & Labeling > Printable Tubing

Printable Tubing Type: **Continuous**Printable Tubing Grade: **Fluid Resistant**Shrink Ratio: **3:1**Primary Product Color: **Yellow**Expanded Inside Diameter (Min): **9.5 mm [.375 in]**

Features

Product Type Features

Printable Tubing Type	Continuous
Printable Tubing Grade	Fluid Resistant

Body Features

Shrink Ratio	3:1
Primary Product Color	Yellow

Dimensions

Expanded Inside Diameter (Min)	9.5 mm[.375 in]
Recovered Inside Diameter (Max)	3.2 mm[.125 in]
Compatible Cable Diameter Range	3.2 – 7.6 mm[.126 – .299 in]

Usage Conditions

Operating Temperature Range	-75 – 135 °C[-103 – 275 °F]
-----------------------------	-----------------------------

Printer/Label Features

Printer Technology	Thermal Transfer
--------------------	------------------

Packaging Features

Packaging Quantity	50
--------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

			
TE Part # 1-2186500-1 T3212-PRINTER	TE Part # 1-2186502-1 T3224-PRINTER	TE Part # 1-2186503-1 T3224-SWARE-PRINTER	TE Part # 1-2186501-1 T3212-SWARE-PRINTER
			
TE Part # 1-2186538-1 RIB-1982-300-110-L-0	TE Part # 1-2186540-1 RIB-1982-300-60-L-0	TE Part # 1-2186549-1 RIB-1982-240-110-L-0-T200	TE Part # CP8122-000 T6112DS-PRINTER

Also in the Series | D-CT



Printable Tubing(16)

Customers Also Bought



TE Part #4-1734839-0
 FPC CONN. 0.5MM PITCH T/C,40P



TE Part #1-1658527-0
 622-2641LF FEM SOCKT,LEAD FREE



TE Part #1658527-7
 622-1641LF FEM SOCKT,LEAD FREE



TE Part #9-1625868-4
 RP 2A 0.25W 49R 0.1% 25PPM 1K RL



TE Part #4-1879350-8
 RR01 5% 20R AMMO



TE Part #T4040014041-000
 M8.MLE.PNLREAR.4POS.STR PCB



TE Part #1513472-5
 UAM Assembly 360mm cable



TE Part #1658527-8
 622-2041LF FEM SOCKT,LEAD FREE



TE Part #EL8093-000
 D-CT-50M-4.8-OUT-4



TE Part #EL8105-000
 D-CT-50M-18-OUT-4

Documents

Product Drawings

[D-CT-50M-9.5-OUT-4](#)

English

[D-CT-50M-9.5-OUT-4](#)

English

Datasheets & Catalog Pages

[Printable Continuous Tubing](#)

English

D-CT, Continuous Diesel Resistant Heat Shrinkable Identification Tube

English

Product Specifications

[Product Specification](#)

English

IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English