TRIPP-LITE

Cat5e 350 MHz Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), PoE - Gray, 200 ft. (60.96 m)

MODEL NUMBER: N001-200-GY



Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 200-ft. Color: gray Connectors: RJ45 male
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair Solid UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available without the snagless feature (N002 series)
- Also available Cat6 cables (N201 series)

Specifications

distance performance Meets most current industry standards including IEEE

Highlights

standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801, and ETL (Category 5e, draft 11)

Cabling for Category 5 (Cat5) and 5e (Cat5e) applications
Solid Conductor wire for long

- Feature molded connectors with integral strain relief. Rated for 350 MHz/ 1 Gbps communication
- Snagless boots protect the locking tabs on the RJ45 connectors from being damaged during installation

System Requirements

 For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

Package Includes

• 200-ft. Gray Snagless Cat5e Patch Cable

OVERVIEW		
UPC Code	037332041937	
Technology	Cat5/5e	
POWER		
Power Over Cable (PoC) Support	No	
PHYSICAL		

TRIPP-LITE

	1
Cable Jacket Color	Gray
Cable Jacket Material	PVC
Cable Jacket Rating	СМ
Cable Shielding	UTP
Cable Outer Diameter (OD)	5.0 mm
Number of Conductors	4 Pair
Conductor Material	Solid Copper
Conductor Gauge	26 AWG
Cable Length (ft.)	200
Cable Length (m)	60.98
Cable Length (in.)	2401.6
Cable Length (cm)	6100
Shipping Dimensions (hwd / in.)	2.00 x 11.00 x 11.00
Shipping Dimensions (hwd / cm)	5.08 x 27.94 x 27.94
Shipping Weight (lbs.)	3.70
Shipping Weight (kg)	1.68
ENVIRONMENTAL	
Operating Temperature Range	14° to 104°F (-10° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
Bandwidth per TIA Standard	100 MHz
Maximum Bandwidth as Tested	350 MHz
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3ab; 802.3at
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Crossover Wiring	No
Contact Plating	Gold
РоЕ Туре	Type 2 PoE+ (30W, IEEE 802.3at)
Connector Type	Molded; Snagless



Wiring Configuration	EIA/TIA 568B	
Angled Connector	No	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
IP68 Rated	No	
Snagless Connector	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Certifications	UL Listed; cUL Listed	
Product Compliance	CE (Europe); RoHS; IEEE 802.3ab 1000Base-T; IEEE 802.3at PoE+; REACH; UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
	•	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.