








Pin	A	B
2	2.00	8.00
3	4.00	10.00
4	6.00	12.00
5	8.00	14.00
6	10.00	16.00
7	12.00	18.00
8	14.00	20.00
9	16.00	22.00
10	18.00	24.00
11	20.00	26.00
12	22.00	28.00
13	24.00	30.00
14	26.00	32.00
15	28.00	34.00
16	30.00	36.00




技术参数

间距: 2.0
温度范围: -25~+85℃
额定电压: 250V AC, DC
额定电流: 2.0A AC, DC
接触电阻: 20mΩ
绝缘电阻: 800MΩ
耐压: 500V AC/minute

线性公差 / General Tolerance
X ±0.2
X.X ±0.1
X.XX ±0.05
角度公差 / Angle Tolerance
X° ±5.0°
X.X° ±3.0°
X.XX° ±1.0°

视角 / Projection



A1	调整平面		
标记	更改内容	签名	年月日
绘图			
审核			
工艺		批准	

材料 / Material

- ①塑座: LCP 本色
②接触针: 黄铜 (镀锡)
③焊片: 黄铜 (镀锡)

单位 (Units)	版本	比例
mm	2.0	1:1
共 1 张	第 1 张	

Bossie (博锡)

品名 / ProduceName

PH2.0 立贴 10P

型号 / Model

BX-PH2.0-10PLT