



Wire & Cable > Hook Up Wire



Cable Type: **Spec 99M**
Voltage Rating: **600 V**
Wire & Cable Insulation Material: **Radiation-Crosslinked, Modified Polyester**
Conductor Material: **Tin-Plated Copper**
Wire Size: **20 AWG**

Features

Product Type Features

Product Type	Cable
Product Classification	Cable - Spec 99 & 100
Cable Style	Primary

Configuration Features

Number of Conductors	1
Number of Strands	19

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Wire & Cable Insulation Material	Radiation-Crosslinked, Modified Polyester
Conductor Material	Tin-Plated Copper
Wire Color (Base)	Black

Dimensions

Wire Diameter	1.3 mm[.051 in]
Overall Outside Diameter	1.5 mm[.059 in]
Conductor Diameter	1.01 mm[.04 in]
Cable Insulation Thickness	.15 mm[.006 in]



Strand Size	32 AWG
Wire Size	.52 mm²

Usage Conditions

Cable Type	Spec 99M
Operating Temperature Range	-55 – 120 °C

Other

Wire Source	United Kingdom
-------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 650074-000
[D-436-36](#)

Customers Also Bought

TE Part #C27444-000
[CM-SCE-TP-1/2-6H-4](#)

TE Part #7308713001
[99M0111-22-9](#)

TE Part #4526713001
[99M0111-16-0](#)

TE Part #4589973001
[99M0111-16-2](#)

TE Part #9727873001
[99M0111-20-2L](#)

TE Part #3665513001
[99M0111-20-4](#)

TE Part #9564073001
[99M0111-20-5](#)

TE Part #7330413001
[99M0111-20-6](#)

Documents

[Datasheets & Catalog Pages](#)
[1654025_Sec9_Type99M](#)

English

[Raychem Wire and Cable Quick Reference Guide](#)
English