




标记 MARK.	更改内容 MODIFICATION	日期 DATE	修改 DRAW	核准 APPROVE

技术要求Specification:

1、材质Material: PA66 UL94V-0;

2、额定电流 Current rating:1.0A AC,DC

3、额定电压 Voltage rating: 50V AC,DC

4、温度范围 Temperature range:-25℃to+85℃

5、接触电阻 Contact resistance:≤30mΩ

6、绝缘电阻 Insulation resistance:≥100MΩ

7、耐 压 Withstand voltage:500V AC/minute

8、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

线数	型 号	尺 寸			
		A	B	C	D
2	SH12512-2Y	1.25	2.00	3.75	---
3	SH12512-3Y	2.50	3.20	5.00	---
4	SH12512-4Y	3.75	4.30	6.25	---
5	SH12512-5Y	5.00	4.30	7.50	6.25
6	SH12512-6Y	6.25	6.25	8.75	8.75
7	SH12512-7Y	7.50	6.25	10.00	8.75
8	SH12512-8Y	8.75	6.25	11.25	8.75
9	SH12512-9Y	10.00	6.25	12.50	8.75
10	SH12512-10Y	11.25	8.30	13.75	10.70
	SH12512-11Y	12.50	8.30	15.00	10.70
	SH12512-12Y	13.75	8.30	16.25	10.70
	SH12512-13Y	15.00	8.30	17.50	10.70
	SH12512-14Y	16.25	8.30	18.75	10.70
	SH12512-15Y	17.50	8.30	20.00	10.70
	SH12512-16Y	18.75	8.30	21.25	---

OTHERWISE SPECIFIED		◀: Inspection Item		 Bossie (博锡)			
. X ± 0.30	X. ° ± 1°	(NO.)	: Cp/Cpk and SPC Control Item				
. XX ± 0.20	. X° ±		材 料 MATERIAL	PA66	名 称 TITLE	GH1.25胶壳-6Pin	
. XXX ± 0.10	. XX° ±	料 厚 THICK		编 号 DWG NO.	BX-GH1.25-6PJK	单 位 UNIT	m m
制 图 DRAWIN		料 宽 WIDE		比 例 SCALE	1:1	版 本 REV.	A
审 核 CHECKED	Zhou qi	日 期 DATE		角 法 PROJ.			规格书
批 准 APPROVE							