



**Product:** [6502GE](#)

Security & Sound, #22-2c, BC, Shielded, CMP

Product Description

Security & Sound Cable, Plenum-CMP, 1-22 AWG stranded bare copper pair with Flamarrest® insulation and Beldfoil® shield, 2-22 AWG stranded bare copper conductors with insulation, overall Flamarrest® jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy Environment
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	22	7x30	BC - Bare Copper
Conductor(s)	2	22	7x30	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.009 in (0.23 mm)	0.047 in (1.2 mm)	Black & Red
Conductor(s)	PVC - Polyvinyl Chloride	0.009 in (0.23 mm)	0.047 in (1.2 mm)	White, Green

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type
Each Pair	Tape	Bi-Laminate (Alum+Poly)	100%	16 AWG (7x24) TC
Conductor(s)	No Shield			

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.155 in (3.94 mm)	Yes

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Pair(s)	17.24 Ohm/1000ft	3.23 Ohm/1000ft (10.6 Ohm/km)	55 pF/ft (180 pF/m)	99 pF/ft (320 pF/m)	2.2 Amps per Conductor at 25°C
Conductor(s)	17.2 Ohm/1000ft (56.4 Ohm/km)				

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature
75°C

Bend Radius

Stationary Min.	Installation Min.
1.55 in (39.4 mm)	1.55 in (39.4 mm)

Max. Pull Tension:	36.4 lbs (16.5 kg)
Bulk Cable Weight:	19 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Outdoor
Flammability / Reaction to Fire:	NFPA 262 (UL910), FT6
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	5502GE

History

Update and Revision:	Revision Number: 0.430 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
6502GE 010C100	Black	612825177661	
6502GE 010U1000	Black	612825177678	
6502GE 008U1000	Gray	612825177623	
6502GE 8771000	Natural	612825177708	C
6502GE 877U1000	Natural	612825177692	
6502GE 009C100	White	612825177630	
6502GE 009U1000	White	612825177647	

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.