



Product: [1315SB](#)

Shipboard Speaker, 4 Conductor 14 AWG TC, CMG-LS

Product Description

Shipboard Speaker, 4 Conductor 14 AWG stranded (41x30) tinned copper conductors, PP insulation, CMG-LS rating, LSZH jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Conductors
14	41x30	TC - Tinned Copper	0.073 in	4
Conductor Count:			4	

Insulation		
Material	Nominal Diameter	Nominal Wall Thickness
PP - Polypropylene	0.095 in	0.011 in

Outer Shield

Type
No Shield

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.333 in	0.052 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
2.42 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
29 pF/ft

Inductance

Nominal Inductance
0.17 $\mu$ H/ft

Current

Max. Recommended Current [A]
17.6 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	105°C
Operating Temperature Range:	-30°C To +105°C

Mechanical Characteristics

Max. Pull Tension:	218.400 lbs
Min. Bend Radius/Minor Axis:	3.5 in

Standards

NEC/(UL) Compliance:	CMG-LS
CEC/C(UL) Compliance:	CMG-ST1
IEEE Compliance:	Std. 45 clause 23
Other Specification:	UL444, ABS Type Approval Certificate 06-HS184641E

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU CE Mark:	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading, Limited Smoke
CSA Flammability:	FT4
IEC Flammability:	IEC 60332-1-2, IEC 60332-3-22
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
1315SB 0101000	Black	Reel	1,000 ft	612825111788

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.251 Revision Date: 11-09-2022
----------------------	--

© 2023 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.