




SECTION A-A

- SPECIFICATIONS
- 1、Current Rating: 1A AC, DC
 - 2、Voltage Rating: 50V AC, DC
 - 3、Temperatuer Range: -25℃~+85℃
 - 4、Contact Resistance: 20mΩ Max
 - 5、Insulation Resistance: 100mΩ Min
 - 6、Withstanding Voltang: 500V AC/minute
 - 7、Material: Wafer LCP UL94-V0
Pin Brass Tin-plated




PCB LAYOUT

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	XD-GH-2PWT-XX	1.25	5.75	3.85
3	XD-GH-3PWT-XX	2.50	7.00	5.10
4	XD-GH-4PWT-XX	3.75	8.25	6.35
5	XD-GH-5PWT-XX	5.00	9.50	7.60
6	XD-GH-6PWT-XX	6.25	10.75	8.85
7	XD-GH-7PWT-XX	7.50	12.00	10.10
8	XD-GH-8PWT-XX	8.75	13.25	11.35
9	XD-GH-9PWT-XX	10.00	14.50	12.60
10	XD-GH-10PWT-XX	11.25	15.75	13.85
11	XD-GH-11PWT-XX	12.50	17.00	15.10
12	XD-GH-12PWT-XX	13.75	18.25	16.35
13	XD-GH-13PWT-XX	15.00	19.50	17.60
14	XD-GH-14PWT-XX	16.25	20.75	18.85
15	XD-GH-15PWT-XX	17.50	22.00	20.10
16	XD-GH-16PWT-XX	18.75	23.25	21.35



Ordering Information



		GENERAL TOLERANCE	制图 DRAWING	03	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
		DIM TOL	审核 CHECK					
		X.X ±0.30	批准 APPROVAL		产品名称 TITLE	GH (1.25) 单排卧贴	版本 REV.	A
		X.XX ±0.20	比例 SCALE		产品料号 PART NO.	XD-GH-NPWT-XX	单位 UNITS	mm
		X.XXX ±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行	日期 MODIFY DATE						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						