

Cat6 Gigabit Molded (UTP) Ethernet Cable (RJ45 M/M), PoE, Gray, 5 ft. (1.52 m)

MODEL NUMBER: N200-005-GY



Ideal for connecting high-speed network components, such as computers, printers, video game systems, Blu-ray™ players, copy machines, routers and modems, in a home or office Cat5/5e/6 application.

Features

The Ideal Solution for All High-Speed Cat5/5e/6 Networking

- Connects high-speed network components, such as computers, printers, video game systems, Blu-ray players, copy machines, routers and modems
- Designed for 1000Base-T, 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice, Token Ring Type 3 and EIA/TIA applications
- Recommended for home or office applications
- Provides high-speed connections up to 550 MHz/1 Gbps
- Flawless signal delivery with minimal near-end crosstalk levels

Premium Construction Ensures Error-Free Signal Transfer

- Manufactured from 24 AWG 4-pair stranded UTP with staggered-pin plug design
- Molded RJ45 connectors and gold-plated copper contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)

Specifications

OVERVIEW	
UPC Code	037332204417
Technology	Cat6; PoE

Highlights

- Premium cabling for Cat5/5e/6 home/office network applications
- Rated for 550 MHz/1 Gbps communication
- 24 AWG 4-pair stranded UTP with PVC jacket
- Gold-plated copper contacts minimize data loss
- Integral strain relief protects connectors from stress and cracking

Package Includes

- N200-005-GY Cat6 Gigabit Molded Patch Cable, Gray, 5 ft.

POWER	
Power Over Cable (PoC) Support	No
PHYSICAL	
Cable Jacket Color	Gray
Cable Jacket Material	PVC
Cable Jacket Rating	CM
Cable Shielding	UTP
Cable Outer Diameter (OD)	6.0 mm
Number of Conductors	4 Pair
Conductor Material	Stranded Copper
Conductor Gauge	24 AWG
Wire Gauge (OD - mm ²)	24
Cable Length (ft.)	5
Cable Length (m)	1.52
Cable Length (in.)	60
Cable Length (cm)	152.4
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	14° to 104°F (-10° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
Bandwidth per TIA Standard	250 MHz
Maximum Bandwidth as Tested	500 MHz
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3an; 802.3at
CONNECTIONS	

PoE Capability	30W (802.3at)
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Crossover Wiring	No
Contact Plating	Gold
PoE Type	Type 2 PoE+ (30W, IEEE 802.3at)
Connector Type	Molded
Wiring Configuration	EIA/TIA 568B
Angled Connector	No
FEATURES & SPECIFICATIONS	
Antibacterial	No
IP68 Rated	No
Snagless Connector	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cUL Listed
Product Compliance	CE (Europe); RoHS; IEEE 802.3an 10GBase-T; IEEE 802.3at PoE+; REACH; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty