

Specification Sheet

Part Number: CTP120

Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install

Tubing provides full coverage where spiral wrap or other coverings may not be suitable

In harsh applications the tubing can provide resistance to crushing, impact, and abrasion

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires



Convoluted Tubing, Slit, 0.5" Dia, PE, Black, 8500 ft/carton

Article Number 169-60506

Type CTP120

Color Black (BK)

Quantity Per carton

Product Description

HellermannTyton's Convoluted Tubing, also known at Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offer's excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.

Short Description

Convoluted Tubing, Slit, 0.5" Dia, PE, Black, 8500 ft/carton

Global Part Name

CTP120-PE-BK

Length L (Imperial) 8500.0

Length L (Metric) 2590.8

Variant Slit

Inner Diameter D (Imperial) 0.516

Inner Diameter D (Metric) 13.11

Diameter D (Imperial) 0.70

Diameter D (Metric) 17.78

Outside Diameter OD (Imperial) 0.70

Outside Diameter OD (Metric) 17.78

Nominal Diameter (Imperial) 0.5

Nominal Diameter (Metric)	12.70
Wall Thickness WT (Imperial)	0.005
Wall Thickness WT (Metric)	0.127
Material	Polyethylene (PE)
Material Shortcut	PE
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	8500
Package Quantity (Metric)	2590.80
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)