

MOSFET Silicon N-Channel MOS



1. Applications

Boost PFC switch, Half bridge or Asymmetric half bridge or Series resonance half bridge and full bridge topologies.
Server power, Telecom power, EV charging, Solar inverter, UPS Application.

2. Features



Low drain-source on-resistance: $R_{DS(on)} = 0.105\Omega$ (typ.)
Easy to control Gate switching
Enhancement mode: $V_{th} = 3$ to 5 V

Table 1 Key Performance Parameters

| Parameter | Value | Unit |
|----------------------|-------|------------|
| $V_{DS} @ T_{j,max}$ | 700 | V |
| $R_{DS(on),max}$ | 120 | m Ω |
| $Q_{g,typ}$ | 55.4 | nC |
| $I_{D,pulse}$ | 90 | A |
| Body diode dv/dt | 50 | V/ns |

3. Packaging and Internal Circuit

| Part Name | Package | Marking |
|--------------|---------|--------------|
| ASW65R120EFD | TO247 | ASW65R120EFD |
| ASA65R120EFD | TO220F | ASA65R120EFD |
| ASR65R120EFD | TOLL-8L | ASR65R120EFD |



Released

1 Maximum ratings

at $T_j = 25^\circ\text{C}$, unless otherwise specified

Table 2 Maximum ratings

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|--|---------------|--------|------|-------|------------------|--|
| | | Min. | Typ. | Max. | | |
| Continuous drain current ¹⁾ | I_D | | - | 30 | A | $T_C=25^\circ\text{C}$ |
| Pulsed drain current ²⁾ | $I_{D,pulse}$ | - | - | 90 | A | $T_C=25^\circ\text{C}$ |
| Avalanche energy, single pulse | E_{AS} | - | - | 1216 | mJ | $T_C=25^\circ\text{C}, V_{DD}=50\text{V}, L=10\text{mH}, R_G=25\Omega$ |
| Avalanche current, single pulse | I_{AR} | - | - | 10.9 | A | $T_C=25^\circ\text{C}, V_{DD}=50\text{V}, L=10\text{mH}, R_G=25\Omega$ |
| MOSFET dv/dt ruggedness | dv/dt | - | - | 36.2 | V/ns | $V_{DS}=0\dots400\text{V}$ |
| Gate source voltage (static) | V_{GS} | -20 | - | 20 | V | static; |
| Gate source voltage (dynamic) | V_{GS} | -30 | - | 30 | V | AC ($f > 1\text{ Hz}$) |
| Power dissipation(TO247) | P_{tot} | - | - | 277.8 | W | $T_C=25^\circ\text{C}$ |
| Power dissipation (TO220F) | P_{tot} | - | - | 36.5 | W | $T_C=25^\circ\text{C}$ |
| Storage temperature | T_{stg} | -55 | - | 150 | $^\circ\text{C}$ | |
| Operating junction temperature | T_j | -55 | - | 150 | $^\circ\text{C}$ | |
| Soldering Temperature Distance of 1.6mm from case for 10s | T_L | | | 260 | $^\circ\text{C}$ | |
| Reverse diode dv/dt ³⁾ | dv/dt | - | - | 50 | V/ns | $V_{DS}=0\dots400\text{V}, I_{SD} \leq I_D, T_j=25^\circ\text{C}$ see table 8 |

Released

¹⁾Limited by $T_{j,max}$. Maximum Duty Cycle $D = 0.50$

²⁾Pulse width t_p limited by $T_{j,max}$

³⁾Identical low side and high side switch with identical R_G

2 Thermal characteristics

Table 3 Thermal characteristics (TO220F)

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|--|------------|--------|------|------|------|----------------------------------|
| | | Min. | Typ. | Max. | | |
| Thermal resistance, junction - case | R_{thJC} | - | - | 3.4 | °C/W | - |
| Thermal resistance, junction - ambient | R_{thJA} | - | - | 62 | °C/W | device on PCB, minimal footprint |

Thermal characteristics(TO247)

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|--|------------|--------|------|------|------|----------------------------------|
| | | Min. | Typ. | Max. | | |
| Thermal resistance, junction - case | R_{thJC} | - | - | 0.45 | °C/W | - |
| Thermal resistance, junction - ambient | R_{thJA} | - | - | 57 | °C/W | device on PCB, minimal footprint |

Released

3 Electrical characteristics

at $T_j=25^\circ\text{C}$, unless otherwise specified

Table 4 Static characteristics

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|----------------------------------|---------------|--------|-------|-------|----------|--|
| | | Min. | Typ. | Max. | | |
| Drain-source breakdown voltage | $V_{(BR)DSS}$ | 655 | - | - | V | $V_{GS}=0V, I_D=250\mu A$ |
| Gate threshold voltage | $V_{(GS)th}$ | 3 | | 5 | V | $V_{DS}=V_{GS}, I_D=250\mu A$ |
| Zero gate voltage drain current | I_{DSS} | - | - | 2 | μA | $V_{DS}=650V, V_{GS}=0V, T_j=25^\circ C$ |
| Gate-source leakage current | I_{GSS} | - | - | 100 | nA | $V_{GS}=30V, V_{DS}=0V$ |
| Drain-source on-state resistance | $R_{DS(on)}$ | - | 0.105 | 0.120 | Ω | $V_{GS}=10V, I_D=14A, T_j=25^\circ C$ |
| Gate resistance (Intrinsic) | R_G | - | 12.6 | - | Ω | $f=1MHz, \text{open drain}$ |

Table 5 Dynamic characteristics

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|------------------------------|--------------|--------|------|------|------|---|
| | | Min. | Typ. | Max. | | |
| Input capacitance | C_{iss} | - | 2657 | - | pF | $V_{GS}=0V, V_{DS}=100V, f=1MHz$ |
| Output capacitance | C_{oss} | - | 89 | - | pF | $V_{GS}=0V, V_{DS}=100V, f=1MHz$ |
| Reverse transfer capacitance | C_{riss} | - | 2 | - | pF | $V_{GS}=0V, V_{DS}=100V, f=1MHz$ |
| Turn-on delay time | $t_{d(on)}$ | - | 29.6 | - | ns | $V_{DD}=400V, V_{GS}=10V, I_D=19A, R_G=2\Omega; \text{see table 9}$ |
| Rise time | t_r | - | 31.3 | - | ns | $V_{DD}=400V, V_{GS}=10V, I_D=19A, R_G=2\Omega; \text{see table 9}$ |
| Turn-off delay time | $t_{d(off)}$ | - | 94.6 | - | ns | $V_{DD}=400V, V_{GS}=10V, I_D=19A, R_G=2\Omega; \text{see table 9}$ |
| Fall time | t_f | - | 9.1 | - | ns | $V_{DD}=400V, V_{GS}=10V, I_D=19A, R_G=2\Omega; \text{see table 9}$ |

Table 6 Gate charge characteristics

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|-----------------------|---------------|--------|------|------|------|--|
| | | Min. | Typ. | Max. | | |
| Gate to source charge | Q_{gs} | - | 15 | - | nC | $V_{DD}=400V, I_D=19A, V_{GS}=0 \text{ to } 10V$ |
| Gate to drain charge | Q_{gd} | - | 20.2 | - | nC | $V_{DD}=400V, I_D=19A, V_{GS}=0 \text{ to } 10V$ |
| Gate charge total | Q_g | - | 55.4 | - | nC | $V_{DD}=400V, I_D=19A, V_{GS}=0 \text{ to } 10V$ |
| Gate plateau voltage | $V_{plateau}$ | - | 5.9 | - | V | $V_{DD}=400V, I_D=19A, V_{GS}=0 \text{ to } 10V$ |



Released

Table 7 Reverse diode characteristics

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|-------------------------------|-----------|--------|-------|------|---------|--|
| | | Min. | Typ. | Max. | | |
| Diode forward voltage | V_{SD} | - | 0.67 | - | V | $V_{GS}=0V, I_F=1A, T_J=25^{\circ}C$ |
| Reverse recovery time | t_{rr} | - | 136.7 | - | ns | $V_R=400V, I_F=17A, di_F/dt=100A/\mu s$; see table 8 |
| Reverse recovery charge | Q_{rr} | - | 0.741 | - | μC | $V_R=400V, I_F=17A, di_F/dt=100A/\mu s$; see table 8 |
| Peak reverse recovery current | I_{rrm} | - | 10.28 | - | A | $V_R=400V, I_F=17A, di_F/dt=100A/\mu s$; see table 8 |


Released

4 Electrical characteristics diagram




Released

Diagram 5: Drain-source breakdown voltage




$V_{BR(DSS)}=f(T_j); I_D=1mA$

Diagram 6: Typ. capacitances




$C=f(V_{DS}); V_{GS}=0V; f=1MHz$

Diagram 7: Typ. On-Resistance vs. Junction Temperature



$R_{ds(on)}=f(T_j); V_{GS}=10V/I_D=14A$


Diagram 8: Safe operating area $T_C=25^\circ C$,



$I_D=f(V_{DS}); T_C=25^\circ C; V_{GS}>7V; D=0; \text{parameter } tp$


Released

Diagram 9: Typ. Power Dissipation




$P_{tot}=f(T_C)$

Diagram 10: Max. transient thermal impedance




$Z_{thJC}=f(t_p)$; parameter: $D=t_p/T$

Diagram 11: Forward characteristics of reverse diode



$I_f=f(V_{DS})$; parameter: T_j

Diagram 12: Typ. Drain-source on-state resistance



$R_{ds(on)}=f(T_j)$; $T_j=25C$, Parameter : V_{gs}

Released

5 Test Circuits

Table 8 Diode characteristics




Table 9 Switching times






Table 10 Unclamped inductive load




6 Package Outlines



| Symbol | 单位 mm | | |
|--------|-------|------|------|
| | Min | Nom | Max |
| A | 4.8 | 5.00 | 5.20 |
| A1 | 3.3 | 3.5 | 3.7 |
| A2 | 2.20 | 2.40 | 2.60 |
| b | 1.00 | 1.2 | 1.40 |
| b1 | 2.90 | 3.10 | 3.30 |
| b2 | 1.90 | 2.10 | 2.30 |
| c | 0.50 | 0.60 | 0.70 |
| e | 5.25 | 5.45 | 5.65 |
| E | 15.2 | 15.7 | 16.2 |
| E1 | 10.2 | 10.7 | 11.2 |
| H | 20.8 | 21 | 21.2 |
| H1 | 19.5 | 20.0 | 20.5 |
| H2 | 4.00 | 4.20 | 4.40 |
| G | 5.60 | 5.80 | 600 |
| ΦP | 3.50 | 3.70 | 3.90 |

Figure1: Outline PG-T0247(CD&HT)


Released



| 项目 | 规范(mm) | |
|----------|--------|-------|
| | MIN | MAX |
| A | 9.70 | 10.30 |
| B | 15.50 | 16.10 |
| B1 | 8.99 | 9.39 |
| C | 4.40 | 4.80 |
| C1 | 2.15 | 2.55 |
| D | 2.50 | 2.90 |
| E | 0.70 | 0.90 |
| F | 0.40 | 0.60 |
| G | 1.12 | 1.42 |
| H | 3.40 | 3.80 |
| L | 12.6 | 13.6 |
| N | 2.34 | 2.74 |
| Q | 3.15 | 3.55 |
| ϕP | 3.00 | 3.30 |

Figure2: Outline PG-TO220F(HT)

Released



| SYMBOL | COMMON | | |
|----------|------------|---------|-------|
| | MILLIMETER | | |
| | MIN. | NOMINAL | MAX. |
| A | 2.20 | 2.30 | 2.40 |
| b | 0.70 | 0.80 | 0.90 |
| b1 | 9.70 | 9.80 | 9.90 |
| b2 | 0.36 | 0.45 | 0.55 |
| b3 | 0.05 | 0.100 | ? |
| b4 | 0.30 | 0.40 | 0.50 |
| b5 | 1.10 | 1.20 | 1.30 |
| b6 | 3.00 | 3.10 | 3.20 |
| c | 0.40 | 0.50 | 0.60 |
| D | 10.28 | 10.38 | 10.55 |
| D1 | 10.98 | 11.08 | 11.18 |
| D2 | 3.20 | 3.30 | 3.40 |
| D3 | 7.15 | | |
| D4 | 3.59 | | |
| D5 | 3.26 | | |
| e | 1.10 | 1.20 | 1.30 |
| E | 9.80 | 9.90 | 10.00 |
| E1 | 7.40 | 7.50 | 7.60 |
| E2 | 0.30 | 0.40 | 0.50 |
| E3 | 8.50 | | |
| E4 | 9.46 | | |
| H | 11.50 | 11.68 | 11.85 |
| H1 | 6.55 | 6.65 | 6.75 |
| K | 4.08 | 4.18 | 4.28 |
| L | 1.60 | 1.90 | 2.10 |
| L1 | 0.50 | 0.70 | 0.90 |
| L2 | 0.50 | 0.60 | 0.70 |
| L3 | 1.00 | 1.20 | 1.30 |
| L4 | 0.13 | 0.23 | 0.33 |
| P | 2.85 | 3.00 | 3.15 |
| θ | 10° REF | | |
| aaa | 0.20 | | |
| ccc | 0.20 | | |
| ddd | 0.25 | | |
| eee | 0.20 | | |

Figure3: Outline PG-TOLL(JQ)

Released

Revision History

| Revision | Date | Subjects (major changes since last revision) |
|----------|------------|---|
| 1.0 | 2020-09-15 | Release version |
| 1.1 | 2022-06-18 | Updated TO247 POD to CD |
| 1.2 | 2022-12-23 | Updated Ciss/Coss/Crss&Trr/Qrr/Irrm, and added electrical characteristics diagram |
| 1.3 | 2023-04-26 | Added TO220F package |
| 1.4 | 2023-08-22 | Added TOLL-8L package |

Released