

Specification Sheet

Part Number: MP5M3.NN3P



Mounting plates allow multiple bundles to run parallel. The mounts are secured using two screws, while the bundles are attached using cable ties in any of the available slots.

Cable Tie Mounting Plate, 0.50" x 6.75", T18-T50 Cable Ties, #6 (M3) Screw, PA66, Natural, 100/pkg

Article Number	151-24519
Type	MP5M3
Color	Natural (NA)
Quantity Per	bag
Product Description	HellermannTyton mounting plates allow multiple cable to be run in parallel. The mount is secured with two screws and the cables are attached to the plate by using a cable tie through any of the available slots.
Short Description	Cable Tie Mounting Plate, 0.50" x 6.75", T18-T50 Cable Ties, #6 (M3) Screw, PA66, Natural, 100/pkg
Global Part Name	MP5M3-PA66-NA

Length L (Imperial)	6.75
Length L (Metric)	171.6
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.5
Width W (Metric)	12.7
Cable Ties	T18 - T50
Height H (Imperial)	0.125
Height H (Metric)	3.2
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.2
Mounting Hole Diameter D (Imperial)	0.15
Mounting Hole Diameter D (Metric)	3.7 mm
Mounting Hole Diameter D Max (Metric)	3.7
Mounting Hole Centers (Imperial)	1.25
Material	Polyamide 6.6 (PA66)

Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).