

Power Cord, C20 to C21 - Heavy-Duty, 20A, 250V, 12 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P035-010



C20 to C21 20A heavy-duty cable connects high-output devices with C19/C22 power connectors commonly found on high-powered IT equipment.

Features

20A C20-to-C21 Power Cable for Network Devices That Require a Heavy-Gauge Connection

This heavy-duty cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a blade server, large router or network switch with a C22 inlet, usually found on high-powered, high-temperature (maximum pin 155°C/311°F) equipment, to a PDU or UPS system. It's an ideal choice for upgrading or replacing the standard power cord provided by the device's manufacturer. The 10-foot (3-meter) length allows you great flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332275011
Device Compatibility	Network Switch; PDU; UPS
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	250
PHYSICAL	
Color	Black

Highlights

- Recommended for powering switches, routers and other high-powered network devices
- 10 ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- C20 to C21 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire manages high power levels required for larger equipment

Package Includes

P035-010 Power Cord, C20 to C21, 10 ft. (3 m), Black

Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2; VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	11mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm ²)	3.31
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	1.00 x 9.00 x 12.75
Shipping Dimensions (hwd / cm)	2.54 x 22.86 x 32.38
Shipping Weight (lbs.)	1.58
Shipping Weight (kg)	0.72
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH, Non-Condensing
Storage Humidity Range	10% to 65% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C21
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	

Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty