

PATG HF 2/18 - Conductor marker carrier



1014053

<https://www.phoenixcontact.com/pc/products/1014053>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker carrier, transparent/black, unlabeled, mounting type: slide-on, cable diameter range: 2 ... 4 mm, lettering field size: 18 x 4 mm

Your advantages

- The PATG HF... sleeve is a captive marker carrier
- These conductor marking systems consist of marker carriers and insert labels
- Comprehensive approvals ensure international use
- The use of high-quality plastics supports the most stringent demands of the rail industry and the automotive industry
- The corresponding UCT-WMT... and UC-WMT... insert labels are used for marking
- Due to the plastic properties of the PATG HF..., high-quality fluid printing of the UC-WMT... with the BLUEMARK... is required

Commercial data

Item number	1014053
Packing unit	1,000 pc
Minimum order quantity	1,000 pc
Product key	BG221A
Catalog page	Page 250 (C-3-2019)
GTIN	4046356779401
Weight per piece (including packing)	0.36 g
Weight per piece (excluding packing)	0.357 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Marker carrier cable
Type	Profile

Dimensions

Width	6.4 mm
Length	18 mm

External dimensions

Outside diameter	2 mm ... 4 mm
------------------	---------------

Material specifications

Color	transparent/black
Material	TPU
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	2 mm ... 4 mm
-------------------------	---------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

PATG HF 2/18 - Conductor marker carrier



1014053

<https://www.phoenixcontact.com/pc/products/1014053>

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	2 years

Mounting

Mounting type	slide-on
---------------	----------

PATG HF 2/18 - Conductor marker carrier



1014053

<https://www.phoenixcontact.com/pc/products/1014053>

Classifications

ECLASS

ECLASS-11.0	27281105
ECLASS-12.0	27281105
ECLASS-13.0	27281105

ETIM

ETIM 8.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PATG HF 2/18 - Conductor marker carrier



1014053

<https://www.phoenixcontact.com/pc/products/1014053>

Accessories

UCT-WMT (18X4) - Conductor marker

0801462

<https://www.phoenixcontact.com/pc/products/0801462>




Conductor marker, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 40

UCT-WMT (18X4) YE - Conductor marker

0801463

<https://www.phoenixcontact.com/pc/products/0801463>



Conductor marker, Sheet, yellow, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 40

PATG HF 2/18 - Conductor marker carrier



1014053

<https://www.phoenixcontact.com/pc/products/1014053>

UCT-WMT (18X4) RD - Conductor marker

0801464

<https://www.phoenixcontact.com/pc/products/0801464>



Conductor marker, Sheet, red, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 40

UCT-WMT (18X4) OG - Conductor marker

0801465

<https://www.phoenixcontact.com/pc/products/0801465>



Conductor marker, Sheet, orange, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 40

PATG HF 2/18 - Conductor marker carrier



1014053

<https://www.phoenixcontact.com/pc/products/1014053>

UCT-WMT (18X4) GN - Conductor marker

0801466

<https://www.phoenixcontact.com/pc/products/0801466>



Conductor marker, Sheet, green, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 40

UCT-WMT (18X4) VT - Conductor marker

0801467

<https://www.phoenixcontact.com/pc/products/0801467>



Conductor marker, Sheet, violet, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 40

PATG HF 2/18 - Conductor marker carrier



1014053

<https://www.phoenixcontact.com/pc/products/1014053>

UCT-WMT (18X4) BU - Conductor marker

0801468

<https://www.phoenixcontact.com/pc/products/0801468>



Conductor marker, Sheet, blue, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 40

UC-WMT (18X4) - Conductor marker

0820293

<https://www.phoenixcontact.com/pc/products/0820293>



Conductor marker, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 24

PATG HF 2/18 - Conductor marker carrier




1014053

<https://www.phoenixcontact.com/pc/products/1014053>

UC-WMT (18X4) YE - Conductor marker

0820303

<https://www.phoenixcontact.com/pc/products/0820303>




Conductor marker, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 24

UC-WMT (18X4) BU - Conductor marker

0821072

<https://www.phoenixcontact.com/pc/products/0821072>



Conductor marker, Sheet, blue, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 24

PATG HF 2/18 - Conductor marker carrier




1014053

<https://www.phoenixcontact.com/pc/products/1014053>

UC-WMT (18X4) RD - Conductor marker

0821085

<https://www.phoenixcontact.com/pc/products/0821085>




Conductor marker, Sheet, red, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 24

UC-WMT (18X4) OG - Conductor marker

0824079

<https://www.phoenixcontact.com/pc/products/0824079>



Conductor marker, Sheet, orange, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 24

PATG HF 2/18 - Conductor marker carrier




1014053

<https://www.phoenixcontact.com/pc/products/1014053>

UC-WMT (18X4) GN - Conductor marker

0824082

<https://www.phoenixcontact.com/pc/products/0824082>




Conductor marker, Sheet, green, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 24

UC-WMT (18X4) VT - Cable marker

0825362

<https://www.phoenixcontact.com/pc/products/0825362>



Cable marker, Sheet, violet, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: insert, cable diameter range: 0.6 ... 22 mm, lettering field size: 18 x 4 mm, Number of individual labels: 24

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com