



Product: [7934A](#)

DataTuff® Cat 5e, 4 Bonded-Pr #24 Sol BC, PO Ins, PE Jkt, OSP BURIAL

[Request Sample](#)

Product Description

Industrial Ethernet Cat 5e, 4 Bonded-Pair 24AWG (Solid) Bare Copper, PO Insulation, PE Outer Jacket, Polymer Gel Waterblocked OSP BURIAL

Technical Specifications

Product Overview

Suitable Applications:	burial, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Construction Details

Conductor					
Element	Size	Stranding	Material	Number of Pairs	Number of Element
Pair(s)	24 AWG	Solid	BC - Bare Copper	4	4

Insulation	
Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Bonded-Pair:	Yes
Waterblocking:	Gel Filled

Outer Jacket		
Material	Nom. Diameter	Ripcord
PE - Polyethylene	0.230 in (5.84 mm)	No
Overall Cable Diameter (Nominal):		0.230 in (5.84 mm)

Electrical Characteristics

Electricals	
Max. Conductor DCR	Max. Capacitance Unbalance
93.8 Ohm/km (28.6 Ohm/1000ft)	150 pF/ft

Delay		
Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
538 ns/100m	45 ns/100m	70%

High Frequency											
Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. SRL (Structural Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]
1	2.0 dB/100m	65.3	62.3	63	60	63.8	60.8	20	23	100 ± 15	102.5 ± 7.5
4	4.1 dB/100m	56.3	53.3	51	49	51.7	48.7	23.6	23	100 ± 15	102.5 ± 7.5
8	5.8 dB/100m	51.8	48.8	46	43	45.7	42.7	25.4	24.5	100 ± 15	101 ± 6
10	6.5 dB/100m	50.3	47.3	43	41	43.8	40.8	26	25	100 ± 15	101 ± 6
16	8.2 dB/100m	47.3	44.3	39	36	39.7	36.7	26	25	100 ± 15	101 ± 6
20	9.3 dB/100m	45.8	42.8	36.5	33.5	37.7	34.7	26	25	100 ± 15	101 ± 6
25	10.4 dB/100m	44.3	41.3	33.9	30.9	35.8	32.8	25.5	24.3	100 ± 15	101 ± 6

31.25	11.7 dB/100m	42.9	39.9	31	28	33.9	30.9	25	23.6	100 ± 15	101 ± 6
62.5	17.0 dB/100m	38.4	35.4	22	19	27.8	24.8	23.5	21.5	100 ± 15	101 ± 6
100	22.0 dB/100m	35.3	32.3	14	11	23.8	20.8	22.5	20.1	100 ± 15	
155	28.1 dB/100m	32.5	29.5	4.4	1.4	19.9	16.9	15.8		100 ± 25	
200	32 dB/100m	30.8	27.8	4	1	17.7	14.7	15		100 ± 25	

Voltage

Voltage Rating
300 V

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C To +75°C	-25°C To +75°C	-40°C To +85°C

Bend Radius

Stationary Min.
1 in (25 mm)

Max. Pull Tension:	40 lbs (18 kg)
Bulk Cable Weight:	22 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Outdoor, Outdoor, Non-Halogenated, Sunlight Resistance, Oil Resistance
CPR Compliance:	CPR Euroclass: Fca
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
Third Party Performance Verification:	Category 5e
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	EtherNet IP is a trademark of ControlNet International Ltd. under license by DeviceNet Vendor Association, Inc. Operating Temperature subject to length de-rating.
--------	--

History

Update and Revision:	Revision Number: 0.537 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
7934A 0101000	Black	Reel	1,000 ft	612825191674

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.