

Specification Sheet

Part Number: DCT90HIRK2



Provides dual separation between bundles to prevent chafing and abrasion.
150lb. tensile strength ensures enough strength for heavy duty applications.
Straps are releasable for increased serviceability.

Dual Clamp Tie, 0.25" Stud Dia, 1.30" Max Bundle Dia, 150lb, PA66HIRHSUV, Black 50/pkg

Article Number	115-30900
Type	DCT9
Color	Black (BK)
Quantity Per	bag
Product Description	Dual-Clamp Ties are designed to provide parallel separation between hoses, wires, cables, and tubing to protect them from abrasion. These ties have an optional mounting hole for securing bundles along the chassis of trucks, trailers, and heavy-duty equipment. The unique one-piece design features the dual head centered on the strap.
Short Description	Dual Clamp Tie, 0.25" Stud Dia, 1.30" Max Bundle Dia, 150lb, PA66HIRHSUV, Black 50/pkg
Global Part Name	DCT9-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	150.0
Minimum Tensile Strength (Metric)	667.0
Length L (Imperial)	13.0
Length L (Metric)	331.0
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.5
Width W (Metric)	12.8
Bundle Diameter Min (Imperial)	0.25
Bundle Diameter Min (Metric)	6.4
Bundle Diameter Max (Imperial)	1.3
Bundle Diameter Max (Metric)	33.0
Height H (Imperial)	0.8

Height H (Metric)	19.1
Stud Diameter (Metric)	M6
Stud Diameter (Imperial)	1/4
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)