

## SCSI/Fibre Channel - 12-ft. SCSI Cable HD68M to HD68M Double Shielded

MODEL NUMBER: **S404-012**



### Highlights

- Premium double-shielded cable
- 34 twisted-pair conductors

### System Requirements

- Any external SCSI device or host controller card requiring HD68 interface

### Package Includes

- 12-ft. SCSI cable HD68M to HD68M double shielded

### Description

Multi-platform SCSI III external peripheral cable HD68M/M. This 12ft cable is designed to connect two SCSI III (fast and wide) or SCSI II devices together. Manufactured using double shielded 34 twisted pair high impedance cable. Constructed with low-capacitance, impedance matched, 28 AWG, stranded, tinned copper cable with insulated in polypropylene. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

### Features

- Backwards compatibility with previous SCSI generations
- Double shielded (foil and braid)
- 34 twisted pair conductors
- Low-capacitance impedance matched 28 AWG stranded tinned copper insulated in polypropylene
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

## Specifications

OVERVIEW	
UPC Code	037332014139
PHYSICAL	
Cable Length (ft.)	12
Cable Length (m)	3.66
Shipping Dimensions (hwd / in.)	6.75 x 7.50 x 1.75

**TRIPP-LITE**by **EATON**

1000 Eaton Boulevard

Cleveland, OH 44122

United States

Shipping Dimensions (hwd / cm)	17.14 x 19.05 x 4.44
Shipping Weight (lbs.)	1.54
Shipping Weight (kg)	0.70
<b>CONNECTIONS</b>	
Side A - Connector 1	HD68 (MALE)
Side B - Connector 1	HD68 (MALE)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

**TRIPP-LITE**by **EATON**

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.