

product description



Highly flexible bus cable (4-core), sold by the meter, unassembled

Industrial Ethernet FC TP Trailing Cable, 2x2 (PROFINET Type C), TP installation cable for Connection to FC outlet RJ45, for cable carrier applications, 4-core, shielded, CAT5, sold by the meter (4 million bending cycles), max. delivery unit 2000 m, minimum order quantity 20 m.

suitability for use	Continuous motion control in a cable carrier
cable designation	2YH (ST) C11Y 2x2x0,75/1,5-100 LI GN VZN FRNC SF/UTP
electrical data	
attenuation factor per length	
• at 10 MHz / maximum	0.06 dB/m
• at 100 MHz / maximum	0.22 dB/m
impedance	
• at 1 MHz ... 100 MHz	100 Ω
relative symmetrical tolerance	
• of the characteristic impedance at 1 MHz ... 100 MHz	15 %
near-end crosstalk per length	
• at 1 MHz ... 100 MHz	0.5 dB/m
transfer impedance per length / at 10 MHz	10 mΩ/m
loop resistance per length / maximum	120 mΩ/m
operating voltage	
• RMS value	80 V
NVP value in percent	66 %
mechanical data	
number of electrical cores	4
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires
type of electrical connection / FastConnect	Yes
core diameter	
• of AWG22 insulated conductor	0.75 mm
outer diameter	
• of inner conductor	0.75 mm
• of the wire insulation	1.5 mm
• of the inner sheath of the cable	3.9 mm
• of cable sheath	6.5 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
material	
• of the wire insulation	polyethylene (PE)
• of the inner sheath of the cable	FRNC
• of cable sheath	PUR (TPE-U)
color	
• of the insulation of data wires	white/yellow/blue/orange
• of cable sheath	green

bending radius	19.5 mm
<ul style="list-style-type: none"> with single bend / minimum permissible 	49 mm
<ul style="list-style-type: none"> with multiple bends / minimum permissible 	100 mm
<ul style="list-style-type: none"> with continuous bending 	
number of bending cycles	4000000; Drag chain suitable for 4 million bending cycles at a bending radius of 100 mm, a speed of 4 m/s and an acceleration of 4 m/s ²
tensile load / maximum	150 N
weight per length	63 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation 	-40 ... +75 °C
<ul style="list-style-type: none"> during storage 	-50 ... +75 °C
<ul style="list-style-type: none"> during transport 	-50 ... +75 °C
<ul style="list-style-type: none"> during installation 	-20 ... +60 °C
<ul style="list-style-type: none"> note 	Electrical properties measured at 20 °C, tests according to DIN VDE 0472
fire behavior	flame resistant according to IEC 60332-1-2
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
<ul style="list-style-type: none"> to mineral oil 	oil resistant according to IEC 60811-2-1 (7x24h/90°C)
<ul style="list-style-type: none"> to grease 	resistant
<ul style="list-style-type: none"> to water 	resistant
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free 	Yes
<ul style="list-style-type: none"> silicon-free 	Yes
wire length / for Industrial Ethernet	
<ul style="list-style-type: none"> with 100BaseTX 	85 m
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; cULus / CMX
UL/ETL style / 600 V Rating	Yes; cRU AWM I A/B 80°C 600V
certificate of suitability	
<ul style="list-style-type: none"> EAC approval 	Yes
<ul style="list-style-type: none"> CE marking 	Yes
<ul style="list-style-type: none"> RoHS conformity 	Yes
standard for structured cabling	Cat5e
Marine classification association	
<ul style="list-style-type: none"> American Bureau of Shipping Europe Ltd. (ABS) 	No
<ul style="list-style-type: none"> French marine classification society (BV) 	No
<ul style="list-style-type: none"> Det Norske Veritas (DNV) 	No
<ul style="list-style-type: none"> Germanische Lloyd (GL) 	No
<ul style="list-style-type: none"> Lloyds Register of Shipping (LRS) 	No
<ul style="list-style-type: none"> Nippon Kaiji Kyokai (NK) 	No
<ul style="list-style-type: none"> Polski Rejestr Statkow (PRS) 	No
reference code	
<ul style="list-style-type: none"> according to IEC 81346-2 	WG
<ul style="list-style-type: none"> according to IEC 81346-2:2019 	WGB
further information / internet-Links	
Internet-Link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAx-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> to website: Industry Online Support 	https://support.industry.siemens.com
last modified:	10/30/2021 

