

## **Specification Sheet**

Part Number: CTP380

Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

In harsh applications the tubing provides resistance to crushing, impact, and abrasion.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.



Convoluted Tubing, Slit, 0.38" Dia, PE, Black, 15000ft/carton

Article Number 169-60514

Type CTP380

Color Black (BK)

Quantity Per carton

Product Description	HellermannTyton's Convoluted Tubing, also known at Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offer's excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.
Short Description	Convoluted Tubing, Slit, 0.38" Dia, PE, Black, 15000ft/carton
Global Part Name	CTP380-PE-BK
Length L (Imperial)	15000.0
Length L (Metric)	4572
Variant	Slit
Inner Diameter D (Imperial)	0.380
Inner Diameter D (Metric)	9.65
Diameter D (Imperial)	0.526
Diameter D (Metric)	13.36
Outside Diameter OD (Imperial)	0.526

13.36

0.38

Outside Diameter OD (Metric)

Nominal Diameter (Imperial)

Nominal Diameter (Metric)	9.65
Wall Thickness WT (Imperial)	0.005
Wall Thickness WT (Metric)	0.127
Material	Polyethylene (PE)
Material Shortcut	PE
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	15,000
Package Quantity (Metric)	4572
Customs Number	3926909988

## About HellermannTyton HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com). © 2023 HellermannTyton. All Rights Reserved. Contact Us RoHS/WEEE Compliance Disclaimer Terms and Conditions