



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M12 MS-FS Double End Cable Assembly BL



M8/M12 Application Type: **Sensor/Actuator**

Number of Positions: **5**

Connector & Keying Code: **A**

Connector Type (End A): **M12 Plug**

Connector Type (End B): **M12 Socket**

[All M12 MS-FS Double End Cable Assembly BL \(18\)](#)

Features

Product Type Features

| | |
|------------------------|------------|
| Connector Type (End A) | M12 Plug |
| Connector Type (End B) | M12 Socket |
| Cable Assembly Type | M12 |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 5 |
|---------------------|---|

Electrical Characteristics

| | |
|-------------------|---------|
| Operating Voltage | 125 VAC |
|-------------------|---------|

Body Features

| | |
|-------------------------|---------------------------------|
| Cable Color | Black |
| Connector Color (End B) | Black |
| Connector Color (End A) | Black |
| Jacket Material | PVC |
| Wire Color (Base) | Brown, White, Blue, Black, Gray |
| Connector & Keying Code | A |

Contact Features

| | |
|------------------------------|-----|
| Contact Current Rating (Max) | 4 A |
|------------------------------|-----|

Mechanical Attachment



| | |
|-------------------------------|-----------|
| Thread Size | M12 x M12 |
| Connector Orientation (End A) | Straight |
| Connector Orientation (End B) | Straight |

Housing Features

| | |
|------------------|---------|
| Housing Material | Plastic |
|------------------|---------|

Dimensions

| | |
|------------------------|-----------------|
| Outside Cable Diameter | 5.2 mm[.204 in] |
| Wire Size | .326 mm² |

Usage Conditions

| | |
|-----------------------------|---------------------------|
| Operating Temperature Range | -30 – 80 °C[-22 – 176 °F] |
|-----------------------------|---------------------------|

Operation/Application

| | |
|-------------------------|-----------------|
| M8/M12 Application Type | Sensor/Actuator |
| Shielded | No |

Packaging Features

| | |
|------------------|-----|
| Packaging Method | Box |
|------------------|-----|

Other

| | |
|------------------------------|--------------|
| Field Serviceable | Yes |
| Cable Assembly Length | 2 m |
| Cable Assembly Configuration | Double Ended |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not applicable for solder process capability |



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2273122-5

M12 angled plug to M12 strgt socket AA

Customers Also Bought



TE Part #1-1563878-1

Heavy Duty Sealed Connector Series Housings



TE Part #TAA755A1611-080

M12A5-MS-FS-PVC-8.0M




TE Part #963531-1

BLINDSTOPFEN



TE Part #964971-1

EINZELLEITERDICHTNG



TE Part #5-1879627-8

H4P 2K4 1% 100PPM



TE Part #969028-5

TAB A 1.6x0.6 CONTACT CS SWS Ag



TE Part #02560231-000

RVDT R30A ASSY



TE Part #C63309-000

B-155-3806



TE Part #1-965983-1
110 FASTON,REC.,20-24 AWG,PTPB

Documents

Product Drawings

M12 strgt plug to M12 strgt socket AA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2273114-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2273114-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2273114-5_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

M8 / M12 Connector System Catalog

Japanese

Product Specifications

Product Specification

English