

ATGBICS F10-QSFP-8LC-AOC5M Extreme Compatible Active Optical Breakout Cable 40G QSFP+ to 4 Duplex LC (5m)

Brand : ATGBICS

Product code: F10-QSFP-8LC-AOC5M-C

Product name : F10-QSFP-8LC-AOC5M Extreme
Compatible Active Optical Breakout Cable 40G QSFP+ to 4
Duplex LC (5m)



F10-QSFP-8LC-AOC5M Extreme Compatible Active Optical Breakout Cable 40G QSFP+ to 4 Duplex LC (5m)

ATGBICS F10-QSFP-8LC-AOC5M Extreme Compatible Active Optical Breakout Cable 40G QSFP+ to 4 Duplex LC (5m):

ATGBICS F10-QSFP-8LC-AOC5M compatible 40GBase QSFP+ to 8xLC active optical cable operates at a wavelength of 850nm over OM3 multimode fibre with a cable length of 5m. It is suitable for short distances and provides a cost-efficient way to connect hardware within close proximity racks. This breakout cable connects to 1 x 40G QSFP+ port of a switch on one end and to 8 x LC connection options on the other end, proving flexible configuration options.. Our product meets the specification of Extreme F10-QSFP-8LC-AOC5M= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards and protocols including; 40G InfiniBand 8x DDR, 4x QDR, 10G/40Gigabit Ethernet, Fibre Channel.



Features		Operational conditions	
Product colour *	Aqua colour	Operating temperature (T-T)	0 - 70 °C
Cable length *	5 m	Storage temperature (T-T)	-40 - 80 °C
Connector 1 *	QSFP+	Operating relative humidity (H-H)	10 - 90%
Connector 1 gender *	Male	Storage relative humidity (H-H)	10 - 85%
Connector 2 gender *	Male	Packaging data	
Jacket material	Optical fiber non-conductive plenum (OFNP)	Quantity per pack	1 pc(s)
Ethernet interface type	40 Gigabit Ethernet	Technical details	
Networking standards	IEEE 802.3ba	Sustainability compliance	✓
AWG wire size	30	Sustainability certificates	RoHS
Data transfer rate	40000 Mbit/s	Doesn't contain	Lead
Plug and Play	✓		
Certification	CE, FCC, RoHS		
Country of origin	United Kingdom		



5056468728074

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 21-SEP-2023. Prints or copies of Information are only valid on the printed Publication date