

product type designation

product description

IE Connecting Cable IE FC RJ45-180 / IE FC RJ45-180

Flexible plug-in cable (4-core), preferred length, preassembled with two IE FC RJ45 connectors 2x2

IE connecting cable IE FC RJ45 Plug-180/IE FC RJ45 Plug-180; IE FC Trailing Cable GP Pre-assembled with 2x IE FC RJ45 plug 180; length 15.0 m.



suitability for use

For connecting Industrial Ethernet stations with an RJ45 interface (10/100 Mbps)

wire length

15 m

electrical data

number of electrical connections

2

attenuation factor per length

- at 10 MHz / maximum
- at 100 MHz / maximum

0.06 dB/m
0.2 dB/m

impedance

- at 1 MHz ... 100 MHz

100 Ω

relative symmetrical tolerance

- of the characteristic impedance at 1 MHz ... 100 MHz

5 %

near-end crosstalk per length

- at 1 MHz ... 100 MHz

0.5 dB/m

transfer impedance per length / at 10 MHz

20 mΩ/m

loop resistance per length / maximum

120 mΩ/m

operating voltage

- RMS value

80 V

NVP value in percent

66 %

mechanical data

number of electrical cores

4

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tinned copper wires

core diameter

- of AWG22 insulated conductor

0.75 mm

outer diameter

- of inner conductor
- of the wire insulation
- of the inner sheath of the cable
- of cable sheath

0.75 mm
1.5 mm
3.9 mm
6.5 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.2 mm

material

- of the wire insulation
- of the inner sheath of the cable
- of cable sheath

polyethylene (PE)
PVC
PVC

color	
<ul style="list-style-type: none"> of the insulation of data wires of cable sheath 	white/yellow/blue/orange green
bending radius	
<ul style="list-style-type: none"> with single bend / minimum permissible with multiple bends / minimum permissible with continuous bending 	32.5 mm 58.5 mm 100 mm
number of bending cycles	3000000; Drag chain suitable for 3 million bending cycles at a bending radius of 100 mm, a speed of 4 m/s and an acceleration of 4 m/s ²
tensile load / maximum	150 N
weight per length	68 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport during installation note 	-25 ... +75 °C -25 ... +75 °C -25 ... +75 °C -10 ... +60 °C Electrical properties measured at 20 °C, tests according to DIN VDE 0472
fire behavior	flame resistant according to UL 1685 (CSA FT 4)
chemical resistance	
<ul style="list-style-type: none"> to mineral oil to grease to water 	conditional resistance Conditional resistance conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free silicon-free 	No Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us, CMG FT4 / (ETL)us PLTC / Sun Res / OIL RES
UL/ETL style / 600 V Rating	Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2
certificate of suitability	
<ul style="list-style-type: none"> EAC approval CE marking RoHS conformity 	Yes Yes Yes
Marine classification association	
<ul style="list-style-type: none"> American Bureau of Shipping Europe Ltd. (ABS) French marine classification society (BV) Det Norske Veritas (DNV) Germanische Lloyd (GL) Lloyds Register of Shipping (LRS) Nippon Kaiji Kyokai (NK) Polski Rejestr Statkow (PRS) 	No No No No No No No
reference code	
<ul style="list-style-type: none"> according to IEC 81346-2 according to IEC 81346-2:2019 	WG WGB
further information / internet-Links	
Internet-Link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool to website: Industrial communication to website: Industry Mall to website: Information and Download Center to website: Selection guide for cables and connectors to website: Image database to website: CAx-Download-Manager to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
last modified:	12/31/2021 