

EMI & EMC Solutions > EMI Shielding > EMI Gaskets > Extruded EMI Gasket Conductive Strip



Gasket Type: Extruded EMI Gasket

Finished Type: Conductive Strip

Binding Material: Fluorosilicone

Filler Material: Nickel Plated Graphite (Ni/C)

Gasket Shape: Solid Round

[All Extruded EMI Gasket Conductive Strip \(56\)](#)

Features

Product Type Features

Closing Force	6.1 N/cm
Finished Type	Conductive Strip
Binding Material	Fluorosilicone
Filler Material	Nickel Plated Graphite (Ni/C)

Electrical Characteristics

Resistance to Petroleum	Yes
Volume Resistivity (Max)	.05 Ω.cm

Body Features

Gasket Type	Extruded EMI Gasket
Gasket Shape	Solid Round

Dimensions

Product Length	1 m[3.28 ft]
----------------	--------------

Outside Diameter	1.6 mm[.062 in]
------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 160 °C[-67 – 320 °F]
-----------------------------	----------------------------

Other

Reuse Limits	Reusable More Than 3 Times
--------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Kemtron 1201 Series



EMI Gaskets(48)

Customers Also Bought



Documents

Product Drawings

[FNG Cord 1.6mm x 1m L](#)

English

Datasheets & Catalog Pages

[Performance Materials brochure](#)

English

[Datasheet - Conductive Elastomers](#)

English

[Product Specifications](#)

[Application Specification](#)

English