



Product: [8917](#)

Lead Wire, #16 Str TC, PVC Ins, AWM 1015 AWM 1230

Request Sample

Product Description

Low Temp Plastic Lead Wire, 16AWG (26x30) Tinned Copper, PVC Insulation, AWM 1015 AWM 1230 CSA TYPE TEW JQA-F 600V 105C

Technical Specifications

Product Overview

|                        |                                                                                                                                    |
|------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Suitable Applications: | inter-connection circuits, internal wiring of computer and electronic equipments, internal wiring of appliances, machine tool wire |
|------------------------|------------------------------------------------------------------------------------------------------------------------------------|

Construction Details

Conductor

| Element      | No. of Elements | Size   | Stranding | Material           |
|--------------|-----------------|--------|-----------|--------------------|
| Conductor(s) | 1               | 16 AWG | 26x30     | TC - Tinned Copper |

Insulation

| Material                 | Nom. Thickness     | Nom. Insulation Diameter |
|--------------------------|--------------------|--------------------------|
| PVC - Polyvinyl Chloride | 0.032 in (0.81 mm) | 0.123 in (3.12 mm)       |

|                                   |                    |
|-----------------------------------|--------------------|
| Overall Cable Diameter (Nominal): | 0.123 in (3.12 mm) |
|-----------------------------------|--------------------|

Electrical Characteristics

Electricals

| Nom. Conductor DCR | Max. Current                              |
|--------------------|-------------------------------------------|
| 4.0 Ohm/1000ft     | Single conductor in free air @ 30°C: 26 A |

Voltage

| UL Voltage Rating |
|-------------------|
| 600 V RMS         |

Mechanical Characteristics

Temperature

| UL Temperature | Operating       |
|----------------|-----------------|
| 105°C          | -30°C To +105°C |

Bend Radius

| Stationary Min.   | Installation Min. |
|-------------------|-------------------|
| 1.23 in (31.2 mm) | 1.23 in (31.2 mm) |

|                    |                |
|--------------------|----------------|
| Max. Pull Tension: | 37 lbs (17 kg) |
| Bulk Cable Weight: | 14 lbs/1000ft  |

Standards and Compliance

|                                  |                  |
|----------------------------------|------------------|
| Environmental Suitability:       | Indoor, Outdoor  |
| Sustainability:                  | CA Prop 65       |
| Flammability / Reaction to Fire: | VW-1             |
| NEC / UL Compliance:             | Article 310, MTW |

|                                |                                                                                                                           |
|--------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| AWM Compliance:                | AWM 1015, AWM 1230, CSA AWM I A/B                                                                                         |
| CEC / C(UL) Compliance:        | TEW                                                                                                                       |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| APAC Compliance:               | China RoHS II (GB/T 26572-2011)                                                                                           |

History

|                      |                                                  |
|----------------------|--------------------------------------------------|
| Update and Revision: | Revision Number: 0.506 Revision Date: 04-19-2023 |
|----------------------|--------------------------------------------------|

Part Numbers

Variants

| Item #       | Color                | Putup Type | Length   | UPC          | Footnote |
|--------------|----------------------|------------|----------|--------------|----------|
| 8917 010100  | Black                | Reel       | 100 ft   | 612825219392 |          |
| 8917 010500  | Black                | Reel       | 500 ft   | 612825348009 |          |
| 8917 0101000 | Black                | Reel       | 1,000 ft | 612825219408 | P        |
| 8917 0105000 | Black                | Reel       | 5,000 ft | 612825219415 | C P      |
| 8917 013100  | Blue, Dark           | Reel       | 100 ft   | 612825219453 |          |
| 8917 013500  | Blue, Dark           | Reel       | 500 ft   | 612825219477 |          |
| 8917 0131000 | Blue, Dark           | Reel       | 1,000 ft | 612825219460 | P        |
| 8917 0135000 | Blue, Dark           | Reel       | 5,000 ft | 612825219484 | C        |
| 8917 001100  | Brown                | Reel       | 100 ft   | 612825219019 |          |
| 8917 0011000 | Brown                | Reel       | 1,000 ft | 612825219026 | P        |
| 8917 0081000 | Gray                 | Reel       | 1,000 ft | 612825219286 | C P      |
| 8917 005100  | Green, Dark          | Reel       | 100 ft   | 612825219194 |          |
| 8917 005500  | Green, Dark          | Reel       | 500 ft   | 612825219217 |          |
| 8917 0051000 | Green, Dark          | Reel       | 1,000 ft | 612825219200 | P        |
| 8917 189100  | Green, Yellow Stripe | Reel       | 100 ft   | 612825219521 | A        |
| 8917 1891000 | Green, Yellow Stripe | Reel       | 1,000 ft | 612825219538 | C A      |
| 8917 003100  | Orange               | Reel       | 100 ft   | 612825219118 |          |
| 8917 0031000 | Orange               | Reel       | 1,000 ft | 612825219125 | P        |
| 8917 002100  | Red                  | Reel       | 100 ft   | 612825219071 |          |
| 8917 002500  | Red                  | Reel       | 500 ft   | 612825219095 |          |
| 8917 0021000 | Red                  | Reel       | 1,000 ft | 612825219088 | C P      |
| 8917 0025000 | Red                  | Reel       | 5,000 ft | 612825219101 | C        |
| 8917 0071000 | Violet               | Reel       | 1,000 ft | 612825219248 | P        |
| 8917 009100  | White                | Reel       | 100 ft   | 612825219316 |          |
| 8917 009500  | White                | Reel       | 500 ft   | 612825219330 |          |
| 8917 0091000 | White                | Reel       | 1,000 ft | 612825219323 | P        |
| 8917 0095000 | White                | Reel       | 5,000 ft | 612825219347 | C        |
| 8917 004100  | Yellow               | Reel       | 100 ft   | 612825219156 |          |
| 8917 0041000 | Yellow               | Reel       | 1,000 ft | 612825219163 | C P      |

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.